



**Multitite FCD grey:
Light and flexible.**

Type FCD is, among others, being used in the building-industry, connection of control panels and protection against rodents. FCD is applied for quick and easy mounting and a light to medium mechanical protection.

Material & Construction:

Construction: Galvanised steel core, square-locked with thin wall convoluted thermoplastic (PVC compound) cover.
Cover specifications: PVC, lead-free according to RoHS.
Temperature: -20 °C to +80 °C, intermittent up to +90°C.
Colour: Grey (black is also available).

Classification according NEN-EN-IEC 61386:
Compression resistance: Class 3, Medium (750 N).
Impact resistance: Class 3, Medium (2 J).
Tensile strength: Class 3, Medium (500 N).
Protection class: IP 67 (dust-proof, water-tight).



Square locked

**ANAMET
MULTITITE**

**CONDUIT
TYPE FCD
GREY**

FCD	Diametre		Bending radius (CL)		Small coil		Standard coil		Large coil		Weight (Kg/m)
	Size	Inside	Outside	Static	Dynamic	Metre	Article No.	Metre	Article No.	Metre	
DN	(mm)	(mm)	(mm)	(mm)		Grey		Grey		Grey	
10	7,0	10,0	30	40	-	-	-	-	50	361.010.5	0,08
12	10,0	14,0	37	50	10	361.012.1	-	-	50	361.012.5	0,14
16	13,0	17,0	45	60	10	361.016.1	-	-	50	361.016.5	0,17
18	15,0	19,0	50	70	10	361.018.1	-	-	50	361.018.5	0,19
20	17,0	21,5	55	80	10	361.020.1	-	-	50	361.020.5	0,23
25	21,2	26,0	70	100	10	361.025.1	-	-	50	361.025.5	0,31
32	28,1	34,0	95	125	10	361.032.1	25	361.032.2	-	-	0,40
40	37,7	44,5	115	160	10	361.040.1	25	361.040.2	-	-	0,60
50	48,4	55,5	135	190	10	361.050.1	25	361.050.2	-	-	0,88

The fittings for Multitite FCD are outlined on pages 2-07 till 2-15.



Size/Multitite	DN	10	12	16	18	20	25	32	40	50	-	-	-
Fittings	ISO	M10 / M12	M12 / M16	M16 / M20	M20	M20	M25	M32	M40	M50 / M63	-	-	-
	PG	7	9	11 / 13,5	13,5	16	21	29	36	48	-	-	-
	NPT	-	-	1/2"	-	1/2"	3/4"	1"	-	-	-	-	-



**Multitite FCD black:
Light and flexible.**

Type FCD is used in the building-industry, connection of control panels and offers protection against rodents. FCD is applied for quick and easy mounting and a light to medium mechanical protection.

Material & Construction:

Construction: Galvanised steel core, square-locked with thin wall convoluted thermoplastic (PVC compound) cover.

Cover specifications: PVC, lead-free according to RoHS, sunlight and UV resistant.

Temperature: -20 °C to +80 °C, intermittent up to +90 °C.

Colour: Black (grey is also available).

Classification according NEN-EN-IEC 61386:

Compression resistance: Class 3, Medium (750 N).

Impact resistance: Class 3, Medium (2 J).

Tensile strength: Class 3, Medium (500 N).

Protection class: IP 67 (dust-proof, water-tight).

**ANAMET
MULTITITE**



**CONDUIT
TYPE FCD
BLACK**

FCD	Diametre		Bending radius (CL)		Small coil		Standard coil		Large coil		Weight
Size	Inside	Outside	Static	Dynamic	Metre	Article No.	Metre	Article No.	Metre	Article No.	(Kg/m)
DN	(mm)	(mm)	(mm)	(mm)		Black		Black		Black	
10	7,0	10,0	30	40	-	-	-	-	50	360.010.5	0,08
12	10,0	14,0	37	50	10	360.012.1	-	-	50	360.012.5	0,14
16	13,0	17,0	45	60	10	360.016.1	-	-	50	360.016.5	0,17
18	15,0	19,0	50	70	10	360.018.1	-	-	50	360.018.5	0,19
20	17,0	21,5	55	80	10	360.020.1	-	-	50	360.020.5	0,23
25	21,2	26,0	70	100	10	360.025.1	-	-	50	360.025.5	0,31
32	28,1	34,0	95	125	10	360.032.1	25	360.032.2	-	-	0,40
40	37,7	44,5	115	160	10	360.040.1	25	360.040.2	-	-	0,60
50	48,4	55,5	135	190	10	360.050.1	25	360.050.2	-	-	0,88

The fittings for Multitite FCD are outlined on pages 2-07 till 2-15.



Size Multitite	DN	10	12	16	18	20	25	32	40	50	-	-	-
Fittings	ISO	M10 / M12	M12 / M16	M16 / M20	M20	M20	M25	M32	M40	M50 / M63	-	-	-
	PG	7	9	11 / 13,5	13,5	16	21	29	36	48	-	-	-
	NPT	-	-	1/2"	-	1/2"	3/4"	1"	-	-	-	-	-