

Nr. 6370ZNU

Spann-Nippel „Unitool“

Gehärtet.
Spann-Nippel auch verwendbar im Unilock-System (Ø 40 mm).



Bestell-Nr.	ØDN	ØD1	ØD2	H	M	T	Gewicht [g]
304352	40	25	10	40,0	M12	4,8	230
304592	40	25	10	40,0	M12	4,8	230
304618	40	25	10	40,0	M12	4,8	230
304634	40	-	-	34,7	M 8	12,0	220

Ausführung:

Best.-Nr. 304352: Nullpunkt-Nippel
 Best.-Nr. 304592: Schwert-Nippel
 Best.-Nr. 304618: Untermaß-Nippel
 Best.-Nr. 304634: Schutz-Nippel

Fertigungsmaße der Nippelaufnahme:

