



**ISO straight fitting, female, nickel plated brass  
(including connection set).**




Thread	UIG/UI Size (inch)	Min. Internal Bore (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	D	E			
M16 x 1,5	5/16"	6,8	35	12	26	-	24	10	812.315.7	6,4
M16 x 1,5	3/8"	9,8	35	12	26	-	24	10	812.316.7	6,6
M20 x 1,5	1/2"	13,9	37	13	29	-	27	10	812.320.7	9,4
M25 x 1,5	3/4"	18,5	40	15	35	-	33	5	812.325.7	12,0
M32 x 1,5	1"	22,8	46	15	45	-	43	5	812.332.7	20,9
M40 x 1,5	1.1/4"	30,8	52	16	54	-	52	2	812.340.7	33,1
M50 x 1,5	1.1/2"	36,8	56	18	63	-	60	2	812.350.7	46,8
M63 x 1,5	2"	47,8	66	20	77	-	74	2	812.363.7	81,2

**ISO 90° fitting, male, nickel plated brass  
(including connection set).**




Thread	UIG/UI Size (inch)	Min. Internal Bore (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	D	E			
M16 x 1,5	5/16"	6,8	32	12	26	42	22	10	812.915.7	9,6
M20 x 1,5	5/16"	6,8	33	13	26	42	22	10	812.914.7	9,8
M16 x 1,5	3/8"	9,8	32	12	26	42	22	10	812.916.7	9,8
M20 x 1,5	3/8"	9,8	33	13	26	42	22	10	812.917.7	10,0
M20 x 1,5	1/2"	13,9	36	13	29	43	27	10	812.920.7	14,4
M25 x 1,5	3/4"	18,5	43	15	35	48	33	5	812.925.7	22,2
M32 x 1,5	1"	22,8	48	15	45	59	42	5	812.932.7	34,2
M40 x 1,5	1.1/4"	30,8	57	16	54	68	51	2	812.940.7	59,9
M50 x 1,5	1.1/2"	36,8	63	18	63	78	60	2	812.950.7	90,9
M63 x 1,5	2"	47,8	74	20	77	96	74	2	812.963.7	149,2

**ISO cable-hose fitting, male, nickel plated brass  
(including connection set).**



Thread	UI/UIG Size (inch)	Clamping Range (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	E	F			
M16 x 1,5	5/16"	4 - 6,8	57	12	26	24	18	10	812.715.7	7,4
M16 x 1,5	3/8"	4 - 8	57	12	26	24	18	10	812.716.7	9,4
M20 x 1,5	3/8"	6 - 9,8	57	12	26	24	22	10	812.717.7	11,1
M20 x 1,5	1/2"	6 - 12	59	12	29	27	22	10	812.720.7	11,5
M25 x 1,5	1/2"	10 - 13,9	62	12	29	27	27	5	812.722.7	13,5
M32 x 1,5	3/4"	13 - 18	70	15	35	33	34	5	812.728.7	23,2
M40 x 1,5	1"	18 - 22,8	83	15	45	43	43	2	812.735.7	35,2
M50 x 1,5	1.1/4"	22 - 30,8	96	15	54	52	55	2	812.745.7	69,8

**ISO cable-hose fitting, male, nickel plated brass, silicone  
insert up to max +260 °C (including connection set).**



Thread	UI/UIG Size (inch)	Clamping Range (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	E	F			
M16 x 1,5	5/16"	4 - 6	50	5	26	24	18	10	812.715.4	7,4
M16 x 1,5	3/8"	4 - 9	50	5	26	24	18	10	812.716.4	9,4
M20 x 1,5	1/2"	4,5 - 12	53	6	29	27	22	10	812.720.4	11,5
M25 x 1,5	1/2"	10 - 13	57	7	29	27	28	5	812.722.4	13,5

**ANACONDA  
MULTIFLEX**

**FITTINGS FOR  
TYPE UIG / UI  
IP 40**