

Anti condensation large heater, EHG

- Description:** Large heater to be fixed preferably in vertical position to prevent condensation. Mounting clip for 35 mm DIN rail (EN60715).
- Heating element:** PTC resistor, self regulating and temperature limiting.
- Material:** Plastic, and anodised aluminium profile.
- Operating temperature:** -40°C to +70°C. The heating capacity is for ambient temperature 20°C.
- Connection:** Plug terminal connection (2 x 0.5-2.5 mm²), available on request with connecting cable (500 mm).
- Protection:** IP 44 supplied with cable; IP 20 supplied without cable and with terminals.
- Approvals:** CE, EAC, cULus_UL Listed.
- Pack quantity:** 1 piece.



Capacity (W)	Starting current (A)	L (mm)	Voltage (V)	Item no.
15	1.1	65	110 - 250 V AC, 50/60 Hz	EHG015
30	1.2	65	110 - 250 V AC, 50/60 Hz	EHG030
45	1.8	65	110 - 250 V AC, 50/60 Hz	EHG045
60	2.5	140	110 - 250 V AC, 50/60 Hz	EHG060
75	4.5	140	110 - 250 V AC, 50/60 Hz	EHG075
100	5.0	140	110 - 250 V AC, 50/60 Hz	EHG100
150	7.5	215	110 - 250 V AC, 50/60 Hz	EHG150

