

Fan heater with thermostat, ECR

- Description:** High performance heater to prevent condensation. The fan assists the natural convection for a better heat distribution. Double insulated. Mounting clip for 35 mm DIN rail (EN60715). Temperature safety cut-out to protect against overheating in case of fan failure, automatic reset. Thermostat control lamp.
- Material:** Plastic according to UL94 V-0.
- Setting range:** 0°C to 60°C.
- Heating element:** PTC resistor, temperature limiting.
- Fan life:** 50.000 h at 25°C.
- Operating temperature:** -45 to +70°C.
- Connection:** 2 pole clamp 2.5 mm², torque 0.8Nm max.
- Protection:** IP 20, Class II (double insulated).
- Approvals:** CE, EAC.
- Finish:** Light grey.
- Pack quantity:** 1 piece.



Capacity (W)	Starting current (A)	Voltage (V)	Item no.
550	13.0	220-240 V AC, 50/60 Hz	ECR550

Voltage (V): 100-120 V AC on request.

