

# MUD

## MILD STEEL, WALL MOUNTED ENCLOSURE



TYPE 1, 3R, 12, 13

**Description:** The MUD range of mild steel wall mounted enclosures is also available in double door versions, and complies with TYPE 1, 3R, 12, 13. There are 6 sizes available. The standard finish is RAL 7035, although other colours and sizes are available on request.

**Material:** Body: 1.4 mm mild steel MUD0608030PER5 / 1.5 mm MUD0801230PER5 and above. Doors: 1.4 mm mild steel / 1.8 mm MUD0801230PER5 and above.

**Body:** Folded and seam welded. Four 8.5 mm diameter holes for wall fixing, pressed out in 20.4 mm diameter x 2 mm depressions to allow air circulation around the rear part of the enclosure.

**Door:** Surface mounted with 130° opening. Concealed removable hinges with captive pin. Two removable mounting profiles in the right hand door. Sealing is ensured by an extruded one piece polyurethane gasket.

**Cable access:** No gland plate openings as standard to maximise sealing and clean lines.

**Lock:** Customized slotted lock for easy opening of the door by using any screwdriver and 90° movement. Espagnolette three point locking. Padlock is available as an accessory.

**Protection:** Complies with TYPE 1, 3R, 12, 13. For outdoor installation the use of a rain hood ARF and 100% polyester paint coating is recommended. The corrosion resistance must be taken into consideration.

**Finish:** RAL 7035 structured powder coating.

**Delivery:** Enclosure with doors, and two door mounting profiles on the right door. Mounting accessories. Earthing facilities.

# MUD

MILD STEEL, WALL MOUNTED ENCLOSURE

---

Enclosure dimensions		
H	W	D
600	800	300
800	1200	300
1000	1000	300
1200	1000	300
1200	1200	300
1400	1000	300