

# T-Series outdoor air conditioner

T-Series outdoor air conditioner

nVent

HOFFMAN

CONNECT AND PROTECT



**Description:** The T-Series outdoor air conditioner has a proven robust design for rugged environments. All standard models are equipped with head pressure control for low ambient operation, compressor heater, coated condenser coil, malfunction switch, thermostat and heater package. The unit is designed for a compact footprint and equipped with easy-mount flanges for simple installation. It is delivered with a cleanable, reusable aluminium mesh filter. Non stainless steel versions are equipped with a heater as standard. All units are equipped with a reliable mechanical thermostat for mounting on the side of an enclosure. Factory thermostat setting for cooler is 27 °C . The factory setting for heater is 13 °C.

**Type of connection:** 1,8 Meter cord with NEMA 5-15 plug.

**Material:** Galvanized steel powder coated or Stainless steel.

**Temperature limits inside:** +20 °C ... +55 °C.

**Temperature limits outside:** -40 °C ... +55 °C.

**Protection:** IP56 | TYPE 4X.

**Finish:** RAL 7035 light-grey, semi-textured powder-coat paint standard. SS version is not painted.