


# UNIVERSAL ROTARY SAFETY EYEBOLT WITH EYE HOOK



2131.23.



## Description:

The universal rotary safety eyebolts with eye hooks with double ball bearing for smooth non-jerking action tipping, rotating and turning. Also rotates 90° in direction of screwing in with full load. Not suitable for extended rotational movement when fully loaded. The special design avoids damage to lifting elements and the valuable load when turning. For ring hoists, slings, cables, hooks etc.

## Note:

Ensure even screw-in surface, threads must be screwed in completely.

## 2131.23. Universal rotary safety eyebolt with eye hook

Order No	Rated carrying capacity [t]	d <sub>2</sub>	f	a	b	c	d	e	g	SW
2131.23.012	0,63	M12	18	13	75	18	40	116	41	36
2131.23.016	1,5	M16	24	20	97	25	46	147	50	41
2131.23.020	2,5	M20	30	28	126	30	61	187	61	55
2131.23.024	4	M24	36	36	150	35	78	227	77	70
2131.23.030	5	M30	45	37	174	40	95	267	93	85
2131.23.036	8	M36	54	49	208	48	100	310	102	90

## Max. carried load "G" in tonnes for various types of attachment

Type of attachment/Arrangement of the suspension points								
Number of lines	1	1	2	2	2 symmetrical	2 asymmetrical	3 and 4 symmetrical	3 and 4 asymmetrical
Angle of inclination/load direction	0-7°	90°	0-7°	90°	0-45°	45-60°	0-45°	45-60°
Order No.	carried load in tonnes							
2131.23.012	0,63	0,63	1,26	1,26	0,88	0,63	0,63	1,32
2131.23.016	1,5	1,5	3,0	3,0	2,1	1,5	1,5	3,15
2131.23.020	2,5	2,5	5,0	5,0	3,5	2,5	2,5	5,25
2131.23.024	4,0	4,0	8,0	8,0	5,6	4,0	4,0	8,4
2131.23.030	6,7	5,0	13,4	10,0	7	5,0	5,0	10,5
2131.23.036	10,0	8,0	20,0	16,0	11,2	8,0	8,0	16,8