


# BALL-LOCK PILOT PIN, WITH TAPERED TIP, HEAVY DUTY

2263.




## 2263. Ball-Lock pilot pin, with tapered tip, heavy duty

d <sub>2</sub> / Order No	d <sub>5</sub>	P	l <sub>1</sub> / Order No	N	I (Order Code character)	71 (D)	80 (E)	90 (F)	100 (G)	110 (H)	125 (J)	140 (K)	150 (L)
10 / (2)	10	5,9 - 9,9	19 (2)	8		●	●	●	●	●			
13 / (3)	12	9,9 - 12,9	19 (2)	10		●	●	●	●	●	●		
16 / (4)	12	12,9 - 15,9	25 (3)	15		●	●	●	●	●	●	●	●
20 / (5)	12	15,9 - 19,9	25 (3)	20		●	●	●	●	●	●	●	●
25 / (6)	12	19,9 - 24,9	25 (3)	25			●	●	●	●	●	●	●
32 / (7)	12	24,9 - 31,9	25 (3)	30			●	●	●	●	●	●	●
40 / (9)	12	31,9 - 39,9	30 (4)	40			●	●	●	●	●	●	●

### Ordering Code (example):

**2263.4G3.1410**



**Shape: round**

P = Ø 14,1 mm

**Punch cutting length: l<sub>1</sub>**

25 mm

**Length: l**

100 mm

**Diameter: d<sub>2</sub>**

16 mm

**Type:**

heavy

**Execution:**

Pilot pin with tapered tip

**Punch:**

without ejector pin

= 1410

**Order No**

= (3)

**Order Code character**

= (G)

**Order No**

= (4)

**Order No**

= (3)

**Order No**

= (6)

= 22

### Material:

HSS

Hardness 62 ± 2 HRC

### Execution:

Shaft and pilot pin fine ground.

Special dimensions on request.