




# 顶料器 法兰固定

2477. .1.02



2477. .1.02 顶料器 法兰固定

订购编号	冲程	开始弹力 [daN]	l	l <sub>1</sub>	a
2477.050.00050.1.02	50	50	200	107	84
2477.050.00100.1.02	50	100	200	107	84
2477.050.00150.1.02	50	150	200	107	84
2477.050.00200.1.02	50	200	200	107	84
2477.080.00050.1.02	80	50	260	137	114
2477.080.00100.1.02	80	100	260	137	114
2477.080.00150.1.02	80	150	260	137	114
2477.080.00200.1.02	80	200	260	137	114