


# 钻套 无凸缘, DIN 179 式样 A

277.



材料:  
 渗碳钢  
 硬度 740 ± 40 HV 10  
 结构:  
 磨直径  $d_1$  和  $d_2$ 。

欲订购其它长度和直径时请向我 公司咨询。

## 277. 钻套 无凸缘, DIN 179 式样 A

$d_1$	$d_2$	分级	$l_1$	6	8	9	10	12	16	20	25	28	30	36	45	56	67
0,9 - 1	3	0.1		●		●											
1,1 - 1,8	4	0.1		●		●											
1,9 - 2,6	5	0.1		●		●											
2,7 - 3,3	6	0.1			●			●	●								
3,4 - 4	7	0.1			●			●	●								
4,1 - 5	8	0.1			●			●	●								
5,1 - 6	10	0.1					●	●	●								
6,1 - 8	12	0.1					●	●	●	●							
8,1 - 10	15	0.1						●	●	●	●						
10,1 - 12	18	0.1						●	●	●	●						
12,1 - 15	22	0.1							●	●	●	●		●			
15,5 - 18	26	0.5							●	●	●	●		●			
18,5 - 22	30	0.5								●	●	●		●	●		
22,5 - 26	35	0.5								●	●	●		●	●		
26,5 - 30	42	0.5									●	●		●	●	●	
30,5 - 35	48	0.5									●	●		●	●	●	
35,5 - 42	55	0.5										●		●	●	●	●
42,5 - 48	62	0.5											●	●	●	●	●

订购示例:

钻套 无凸缘, DIN 179 式样 A	=	277.1.
导向装置直径 $d_1$	12.1 mm =	1210.
长度 $l_1$	16 mm =	016
订购编号	=	277.1. 1210.016