

PRECISION FLAT AND SQUARE BAR STEEL, DIN 59350

2922.2842.



Material:


1.2842 / 90 MnCrV
Cold worked steel

Execution:

Thickness precision ground, width ground or milled, length machined

Note:

- = available in 500 mm and 1000 mm lengths
- = only available in 500 mm lengths



2922.2842. Precision flat and square bar steel, DIN 59350

s	1	2	3	4	5	6	8	10	12	15	16	20	25	30	40	50	60
b																	
4				○													
5					○												
6						●											
8							●										
10	○	●	●	●	●	●	●	●									
12	○	●	●	●	●	●	●	●	●								
15	○	●	●	●	●	●	●	●	●	●							
16											●						
20	○	●	●	●	●	●	●	●	●	●		●					
25	○	●	●	●	●	●	●	●	●	●		●	●				
30	○	●	●	●	●	●	●	●	●	●		●	●	●			
35	○	●	●	●	●	●	●	●	●	●		●	●	●			
40	○	●	●	●	●	●	●	●	●	●		●	●	●	●		
50	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	
60	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
70	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
80	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
100	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
120	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
125	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
150	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
160	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
180	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
200	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
250	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
300	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●

Ordering Code (example):

Precision flat and square bar steel, DIN 59350	=	2922.2842.
Width B	50 mm =	050.
Thickness S	1 mm =	001.
Length L	500 mm =	0500
Order No	=	2922.2842. 050. 001. 0500