






# SÜRTÜNME PLAKASI, BRONZ, YAĞ KANALLI, CNOMO



2960.54.45.



2960.54.45.



## Malzeme:

Bronz

## Not:

Civatalar dahil değildir.

## Sabitleme:

Soket başlı vida kullanınız  
DIN EN ISO 4762 M10.

## 2960.54.45. Sürtünme Plakası, Bronz, yağ kanallı, CNOMO

Sipariş No.	Şekil	b	a	e	e <sub>1</sub>	e <sub>2</sub>	e <sub>3</sub>	e <sub>4</sub>	e <sub>5</sub>	e <sub>6</sub>	e <sub>7</sub>	e <sub>8</sub>	e <sub>9</sub>	Vida Deliği adedi
2960.54.45.070.100	A	70	100	20	-	-	-	70	-	-	-	-	10	2
2960.54.45.070.150	B	70	150	10	20	-	-	70	120	-	-	-	10	3
2960.54.45.150.150	H	150	150	25	75	100	45	95	120	-	-	-	50	4
2960.54.45.100.100	I	100	100	30	50	-	-	45	70	-	-	-	25	3