



SÜRTÜNME PLAKASI, BRONZ KENDINDEN YAĞLAMALI, ~VDI 3387




2960.84.



2960.84.



B



Malzeme:

Bronz Kendinden Yağlamalı

Not:

Civatalar dahil değildir.

Sabitleme:

Soket başlı vida kullanınız DIN EN ISO 4762 M8.

2960.84. Sürtünme Plakası, Bronz Kendinden Yağlamalı, ~VDI 3387

Sipariş No.	Şekil	b	l ₁	l ₂	l ₃	l ₄	l ₅	d	d ₁	t	Delik adedi
2960.84.080.200	A	80	200	25	175	-	-	9	15	9	2
2960.84.080.250	B	80	250	25	85	165	225	9	15	9	4
2960.84.080.300	B	80	300	25	105	195	275	9	15	9	4
2960.84.080.350	B	80	350	25	125	225	325	9	15	9	4
2960.84.080.400	B	80	400	25	145	255	375	9	15	9	4
2960.84.080.450	B	80	450	25	165	285	425	9	15	9	4
2960.84.080.500	B	80	500	25	175	325	475	9	15	9	4