




SÜRTÜNME PLAKASI, BRONZ KENDİNDEN YAĞLAMALI, VDI 3357



2960.93.



Malzeme:

Bronz Kendinden Yağlamalı

Not:

Civatalar dahil değildir.

Sabitleme:

Soket başlı vida kullanınız
DIN EN ISO 4762 M12.

2960.93. Sürtünme Plakası, Bronz Kendinden Yağlamalı, VDI 3357

Sipariş No.	b	l ₁	l ₂
2960.93.050.250	50	250	60
2960.93.050.300	50	300	80
2960.93.050.350	50	350	100
2960.93.050.400	50	400	120
2960.93.050.450	50	450	140
2960.93.050.500	50	500	150
2960.93.080.250	80	250	60
2960.93.080.300	80	300	80
2960.93.080.350	80	350	100
2960.93.080.400	80	400	120
2960.93.080.450	80	450	140
2960.93.080.500	80	500	150
2960.93.100.250	100	250	60
2960.93.100.300	100	300	80
2960.93.100.350	100	350	100
2960.93.100.400	100	400	120
2960.93.100.450	100	450	140
2960.93.100.500	100	500	150
2960.93.125.250	125	250	60
2960.93.125.300	125	300	80
2960.93.125.350	125	350	100
2960.93.125.400	125	400	120
2960.93.125.450	125	450	140
2960.93.125.500	125	500	150
2960.93.160.250	160	250	60
2960.93.160.300	160	300	80
2960.93.160.350	160	350	100
2960.93.160.400	160	400	120
2960.93.160.450	160	450	140
2960.93.160.500	160	500	150