


FÜHRUNGSLASTE MIT EINER GLEITFLÄCHE, BRONZE MIT FESTSCHMIERSTOFF



2962.79.



Werkstoff:

Bronze mit Festschmierstoff,
wartungsarm

Hinweis:

Lieferung ohne Schrauben.

2962.79. Führungsleiste mit einer Gleitfläche, Bronze mit Festschmierstoff

Bestell-Nummer	Form	b	s	a	e	e ₁	e ₂	d	Anzahl Bohrungen
2962.79.030.040.150	A	30	40	150	20	50	-	14	3
2962.79.030.040.200	A	30	40	200	20	75	-	14	3
2962.79.030.040.250	B	30	40	250	20	75	50	14	4
2962.79.040.040.150	A	40	40	150	20	50	-	14	3
2962.79.040.040.200	A	40	40	200	20	75	-	14	3
2962.79.040.040.250	B	40	40	250	20	75	50	14	4
2962.79.045.050.150	A	45	50	150	25	50	-	18	3
2962.79.045.050.200	A	45	50	200	25	75	-	18	3
2962.79.045.050.250	B	45	50	250	25	75	50	18	4
2962.79.055.050.150	A	55	50	150	25	50	-	18	3
2962.79.055.050.200	A	55	50	200	25	75	-	18	3
2962.79.055.050.250	B	55	50	250	25	75	50	18	4
2962.79.060.050.150	A	60	50	150	25	50	-	18	3
2962.79.060.050.200	A	60	50	200	25	75	-	18	3
2962.79.060.050.250	B	60	50	250	25	75	50	18	4
2962.79.070.050.150	A	70	50	150	25	50	-	18	3
2962.79.070.050.200	A	70	50	200	25	75	-	18	3
2962.79.070.050.250	B	70	50	250	25	75	50	18	4