




DryLin® WSRM | Trapezoidal Lead Screw Nuts



Structure – Part No.

W S R M-22 15 TR10x2



Material:

W for iglidur® W300

J for iglidur® J*

mm

Threaded Nuts

Phone +49 - 22 03 - 96 49-145
Fax +49 - 22 03 - 96 49-334

iglus® GmbH
51147 Cologne

Internet www.igus.de
E-mail info@igus.de

Dimensions [mm]

Part No.	Supporting surface [mm²]	d1	d2	b1	TR d1 x P	Max. static F [N]
Short Version						
WSRM-2215TR10x2	212	10	22	15	TR 10 x 2	1060
WSRM-2215TR10x3	200	10	22	15	TR 10 x 3	1000
WSRM-2618TR12x3	296	12	26	18	TR 12 x 3	1480
WSRM-3021TR14x4	396	14	30	21	TR 14 x 4	1980
WSRM-3624TR16x2	564	16	36	24	TR 16 x 2	2820
WSRM-3024TR16x4	526	16	30	24	TR 16 x 4	2630
WSRM-3624TR16x4	526	16	36	24	TR 16 x 4	2830
WSRM-3027TR18x4	678	18	30	27	TR 18 x 4	3390
WSRM-4027TR18x4	678	18	40	27	TR 18 x 4	3390
WSRM-3025TR20x4	706	20	30	25	TR 20 x 4	3530
WSRM-4530TR20x4	848	20	45	30	TR 20 x 4	4240
WSRM-5036TR24x5	1214	24	50	36	TR 24 x 5	6070
WSRM-5039TR26x5	1438	26	50	39	TR 26 x 5	7190
WSRM-6042TR28x5	1680	28	60	42	TR 28 x 5	8400
WSRM-6045TR30x6	1906	30	60	45	TR 30 x 6	9530
Long Version						
WSRM-2220TR10x2	282	10	22	20	TR 10 x 2	1410
WSRM-2220TR10x3	266	10	22	20	TR 10 x 3	1330
WSRM-2624TR12x3	394	12	26	24	TR 12 x 3	1970
WSRM-3028TR14x4	526	14	30	28	TR 14 x 4	2630
WSRM-3632TR16x2	702	16	36	32	TR 16 x 2	3510
WSRM-3632TR16x4	752	16	36	32	TR 16 x 4	3760
WSRM-4036TR18x4	904	18	40	36	TR 18 x 4	4520
WSRM-4540TR20x4	1130	20	45	40	TR 20 x 4	5650
WSRM-5048TR24x5	1620	24	50	48	TR 24 x 5	8100
WSRM-5052TR26x5	1918	26	50	52	TR 26 x 5	9590
WSRM-6056TR28x5	2240	28	60	56	TR 28 x 5	11200
WSRM-6060TR30x6	2542	30	60	60	TR 30 x 6	12710

* Trapezoidal lead screw nuts made from iglidur® J in various sizes are available upon request

Custom solutions

The dimensions listed above are available ex stock. Furthermore, we offer a various number of costum parts, materials and threads. Please consult iglus® for your special application.