


**Standard separator, wide foot**

unassembled	<b>21.1</b>
assembled	<b>21.1.1</b>

### Standard - for all applications

Separator with wide foot for maximum locking strength and safe standing in E-Chains®.




**Separator, narrow head**

unassembled	<b>21.2</b>
assembled	<b>21.2.1</b>

### For even faster installation

Firm hold to one side with a wide foot, narrow on opposed side for easy cable assembly (slight grip).

Available upon request. Delivery time approx. 1-2 weeks after order.




**Separator, narrow foot**

unassembled	<b>21.3</b>
assembled	<b>21.3.1</b>

### For many thin cables

Separator with narrow foot for a large number of thin cables side by side. Saves space in E-Chains®.

Available upon request. Delivery time approx. 1-2 weeks after order.




**Separator, asymmetrical**

unassembled	<b>21.4</b>
assembled	<b>21.4.1</b>

### For side-mounted applications

Asymmetrical separator, for defined distance. No additional spacers necessary.

Available upon request. Delivery time approx. 1-2 weeks after order.



**Full-width shelf, lockable**

unassembled	<b>2300.X</b>
assembled	<b>2310.X</b>

### Horizontal separation

Full-width shelf locks safely into separators on both ends, fixed width possible. Separators can be moved freely over the shelf in horizontal direction. Usable in 1 level.

Available upon request. Delivery time approx. 1-2 weeks after order.

### Lockable full-width shelves - for the standard interior separation



Width X [mm]	unassembled	assembled	Width X [mm]	unassembled	assembled	Width X [mm]	unassembled	assembled
011	2300.11	2310.11	060	2300.60	2310.60	087	2300.87	2310.87
025	2300.25	2310.25	062	2300.62	2310.62	090	2300.90	2310.90
030	2300.30	2310.30	065	2300.65	2310.65	100	2300.100	2310.100
038	2300.38	2310.38	070	2300.70	2310.70	103	2300.103	2310.103
040	2300.40	2310.40	075	2300.75	2310.75	110	2300.110	2310.110
050	2300.50	2310.50	077	2300.77	2310.77	120	2300.120	2310.120
057	2300.57	2310.57	080	2300.80	2310.80	125	2300.125	2310.125