



Slotted separator for E-Chains®

unassembled	202
assembled	212

Slotted separator 202 (E-Chains® only)

is used when vertical and horizontal separation is required. Due to its slot, it allows basic vertical/horizontal shelving arrangements.

Slotted separator for E-Tubes

unassembled	24501
assembled	24511

Slotted separator 24501 (E-Tubes only)

is used when vertical and horizontal separation is required. Due to its slot, it allows basic vertical/horizontal shelving arrangements.

Separator, wide foot* for E-Chains®

unassembled	201.28
assembled	211.28

Separator, wide foot* 201.28 (E-Chains® only)

If a wide space between the separators has to be kept or separators have to be fixed in their position, e.g. for side-mounted applications. (*for side-mounted applications)

Side plate for E-Chains®

unassembled	203
assembled	213

Side plate 203 (E-Chains® only)

Side plate for use with full-width shelf 220.X and slotted separator 202.

Spacer* for E-Chains®

unassembled	205.09
assembled	215.09

Spacer* 205.09 (E-Chains® only)

Separators can be fixed in position (only mountable along the inner radius of the fixed crossbar), (*for side-mounted applications)

Full-width shelf for E-Chains®/E-Tubes

unassembled	220.X
assembled	221.X

Full-width shelf 220.X (E-Chains® and E-Tubes)

This option makes sense in applications with many thin cables with similar diameters. For a consequent subdivision. Full-width shelves can be arranged at 3 different heights (in 5 mm increments).

Full-width shelves

Width X [mm]	unassembled	assembled	Width X [mm]	unassembled	assembled	Width X [mm]	unassembled	assembled
025	220.25	221.25	077	220.77	221.77	125	220.125	221.125
038	220.38	221.38	090	220.90	221.90			
057	220.57	221.57	103	220.103	221.103			

