



Slotted middle plate E-Chains®
 unassembled **262**
 assembled **263**

Middle plate 262 (E-Chains® only)

form the basic pattern of shelf 2200.X arranged at 5 different heights (in 5 mm increments)

Slotted separator for E-Chains®
 unassembled **266**
 assembled **267**

Slotted separator 266 (E-Chains® only)

For a very fine subdivision. No retrofitting into an existing separation system without dismantling the interior separators first.

Open slotted separator E-Chains® / E-Tubes
 unassembled **276**
 assembled **277**

Open slotted separator 276 (E-Chains® and E-Tubes)

Quick assembly - retrofitting into an existing interior separation system without dismantling.

Side plate for E-Chains®
 unassembled **264**
 assembled **265**

Side plate 264 (E-Chains® only)

Like middle plate. Allows a pattern system until side links.

Shelf for E-Chains® / E-Tubes
 unassembled **2200.X**
 assembled **2210.X**

Shelf 2200.X (E-Chains® and E-Tubes)

For applications involving many cables with different diameters shelves can be arranged elevator-shifted. They can be arranged at 5 different heights (in 5 mm increments).

Shelves

Width X [mm]	unassembled	assembled	Width X [mm]	unassembled	assembled	Width X [mm]	unassembled	assembled
018	2200.18	2210.18	038	2200.38	2210.38	068	2200.68	2210.68
023	2200.23	2210.23	043	2200.43	2210.43	073	2200.73	2210.73
028	2200.28	2210.28	048	2200.48	2210.48	088	2200.88	2210.88
033	2200.33	2210.33	058	2200.58	2210.58	099	2200.99	2210.99

Strain relief separator for E-Chains®
 unassembled **262.Z**
 assembled **263.Z**

Additional elements for interior separation

Strain relief separator 262.Z (E-Chains® only)

Can be integrated into the mounting bracket and can be placed there at any point. It combines strain relief and interior separation.