



		Separator for E-Chains® unassembled T2102 assembled T2112
		Notch separator for E-Chains® unassembled T2101 assembled T2111
		Strain relief separator for E-Chains® unassembled T2103.Z assembled T2113.Z
		Full-width shelf (30-120 mm) unassembled 110.X assembled 111.X

Standard separator T2102

is used when vertical and horizontal separation is required. Due to its slot, it allows basic vertical/horizontal shelving arrangements.

Notch separator T2101

can be locked in 2 mm increments due to gaps on the crossbars of E-Chains®. The separator cannot slide sideways during the operation.

Strain relief separator T2103.Z

can be integrated into the mounting bracket and can be placed there at any point of the E-Chain®. It combines strain relief and interior separation.

Full-width shelf 110.X

this option makes sense in applications with many thin cables with similar diameters. Full-width shelves can be arranged at 3 different heights (in 5 mm increments).

Full-width shelf

Width X [mm]	unassembled	assembled	Width X [mm]	unassembled	assembled	Width X [mm]	unassembled	assembled
030	110.30	111.30	070	110.70	111.70	110	110.110	111.110
040	110.40	111.40	080	110.80	111.80	120	110.120	111.120
050	110.50	111.50	090	110.90	111.90			
060	110.60	111.60	100	110.100	111.100			

