

Gliding feed-throughs

Gliding feed-through, only for TL.30.05	Gliding feed-through, only for TR.40.05 + TR.60-85.05	Gliding feed-through, only for TR.50.05 + TR.100.05-TR.125.05
<ul style="list-style-type: none"> ● The gliding feed-through enables easy guidance of the e-chain® and can also be used as an additional guide ● Gliding feed-through with swivel bearing ►Page 754 		

Gliding feed-through | For TRC·TRE·TRCF



Ø Index	Part No. Gliding feed-through	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	G [mm]
30.	► TL.30.05	56	60	36	28	14	36	5.8
40.	► TR.40.05.M6 ¹⁾	85	84.5	46	32	21	27	6.5
50.	► TR.50.05.M6 ¹⁾	96	102	58	67	21	27	6.5
60.	► TR.60.05.M8 ¹⁾	126	126	70	50	32	40	9
65.	► TR.65.05.M8 ¹⁾	126	126	75	75	32	40	9
70.	► TR.70.05.M8 ¹⁾	153	155	86	70	35	40	9
85.	► TR.85.05.M8 ¹⁾	153	155	100	84	35	40	9
85. (R 240)	► TR.85.05.M8 ¹⁾	153	155	100	84	35	40	9
100.	► TR.100.05.M8 ¹⁾ *	162.5	169.5	115	85	28	40	8.5
125.	► TR.125.05.M8 ¹⁾	179	190	142	84	40	64	9

*TR.100.05 mit 3 Bohrungen

Standard: through holes in Ø G - 1) Option: with insert nuts, steel, M6/M8