

Triflex® R protectors - high safety under extreme operating conditions

- To achieve long life cycles under heavy loads resulting from impact or friction on the robot's E-Chains®, optional protectors can be fitted at the contact points
- Easy assembly and quick replacement
- Abrasion-resistant TPU material
- Absorptive
- Light
- Easy gliding over edges
- Free positioning on any chain link
- Fast-closing protector available

For Series	Part No. protector	Part No. fast-closing protector	Ø D [mm]	A [mm]
TRC/TRE.40	▶ TR.40.10	upon request	55	27
TRC/TRE.60	▶ TR.60.10	upon request	80	40
TRC/TRE.70	▶ TR.70.10	upon request	102	50
TRC/TRE.85	▶ TR.85.10	TR.85.30 *NEW	118	59
TRC/TRE.100	▶ TR.100.10	upon request	133	67
TRC/TRE.125	▶ TR.125.10 *NEW	upon request	170	82

*NEW in this catalog



Triflex® R

Triflex® R cover variants: Heat protector - TR.XX.15

- Protection against weld spatter and metal splashes at temp. of up to 600°C (short-term)
- Base support: Fabric
- Coating: Aramid
- Easy to replace via longitudinally positioned velcro fastenings
- Elastic sealing strips
- Asbest-free
- Standard lengths available ex stock

For Series	TR.XX.15 Part No.	Standard lengths [mm]
	[YY] = Jacket length	
TRC/TRE/TRL.40	▶ TR.40.15. [YY]	500 1000 1500 2000
TRC/TRE/TRL.60	▶ TR.60.15. [YY]	500 1000 1500 2000
TRC/TRE/TRL.70	▶ TR.70.15. [YY]	500 1000 1500 2000
TRC/TRE.85	▶ TR.85.15. [YY]	500 1000 1500 2000
TRC/TRE/TRL.100	▶ TR.100.15. [YY]	500 1000 1500 2000



TR.XX.15

Standard-protector - TR.XX.16

- Temperature up to room temp.
- Base support: Fabric
- Coating: None
- Easy to replace via longitudinally positioned velcro fastenings
- Elastic sealing strips
- Silicon-free
- Standard lengths available ex stock

For Series	TR.XX.16 Part No.	Standard lengths [mm]
	[YY] = Jacket length	
TRC/TRE/TRL.40	▶ TR.40.16. [YY]	500 1000 1500 2000
TRC/TRE/TRL.60	▶ TR.60.16. [YY]	500 1000 1500 2000
TRC/TRE/TRL.70	▶ TR.70.16. [YY]	500 1000 1500 2000
TRC/TRE.85	▶ TR.85.16. [YY]	500 1000 1500 2000
TRC/TRE/TRL.100	▶ TR.100.16. [YY]	500 1000 1500 2000



TR.XX.16

Light-protector - TR.XX.17

- Temperature up to room temp.
- Base support: Fabric (spun-bonded web)
- Coating: None
- Easy to replace via longitudinally positioned velcro fastenings
- Elastic sealing strips
- Silicon-free
- Standard lengths available ex stock

For Series	TR.XX.17 Part No.	Standard lengths [mm]
	[YY] = Jacket length	
TRC/TRE/TRL.40	▶ TR.40.17. [YY]	500 1000 1500 2000
TRC/TRE/TRL.60	▶ TR.60.17. [YY]	500 1000 1500 2000
TRC/TRE/TRL.70	▶ TR.70.17. [YY]	500 1000 1500 2000
TRC/TRE.85	▶ TR.85.17. [YY]	500 1000 1500 2000
TRC/TRE/TRL.100	▶ TR.100.17. [YY]	500 1000 1500 2000



TR.XX.17

Phone +49- (0) 22 03-96 49-800
Fax +49- (0) 22 03-96 49-222



▶ 5.407-409



For your online order, more products variety and configuration also use
▶ www.Triflex-R.eu