


Adjustable L-couplings with lock nut

Thread:
metric fine thread,
ISO 6149
straight

Sealed with O-ring



Series	Pressure	d2	SW2	SW3	SW4	l1*	l2	l3	i	Nm	kg/100	Order No.	Order No.
Tube OD						approx.				-10 %	approx.	Single component	**
d1													
L 6	PN 315	M 10 x 1	14	14	14	29	14	20	7	15	4.8	1 1 46 00 20 81***	1 1 46 00 20 XX
L 8	PN 315	M 12 x 1.5	17	17	17	31	16	22	10	25	6.9	1 1 46 05 20 81	1 1 46 05 20 XX
L 10	PN 315	M 14 x 1.5	17	19	19	32	17	25	10	35	7.0	1 1 46 10 20 81	1 1 46 10 20 XX
L 12	PN 315	M 16 x 1.5	19	22	22	34	19	26	10	40	10.6	1 1 46 15 20 81	1 1 46 15 20 XX
L 15	PN 315	M 18 x 1.5	19	27	24	36	21	30	11	45	12.2	1 1 46 20 20 81	1 1 46 20 20 XX
L 18	PN 315	M 22 x 1.5	27	32	27	43	26.5	33	12	60	25.4	1 1 46 25 20 81	1 1 46 25 20 XX
L 22	PN 160	M 27 x 2	27	36	32	44	27.5	35	14	100	****	1 1 46 30 20 81	1 1 46 30 20 XX
L 28	PN 160	M 33 x 2	36	41	41	47	30.5	38	14	160	****	1 1 46 35 20 81	1 1 46 35 20 XX
L 35	PN 160	M 42 x 2	41	50	50	58	34.5	48	14	210	****	1 1 46 40 20 81	1 1 46 40 20 XX
L 42	PN 160	M 48 x 2	50	60	55	63	40	49	16	260	****	1 1 46 45 20 81	1 1 46 45 20 XX
S 6	PN 400	M 12 x 1.5	17	17	17	31	16	22	10	35	7.5	1 1 46 50 20 81	1 1 46 50 20 XX
S 8	PN 400	M 14 x 1.5	17	19	19	32	17	26	10	45	8.9	1 1 46 55 20 81	1 1 46 55 20 XX
S 10	PN 400	M 16 x 1.5	19	22	22	36	19.5	27	11	55	13.4	1 1 46 60 20 81	1 1 46 60 20 XX
S 12	PN 400	M 18 x 1.5	27	24	24	41	24.5	31	12	70	26.7	1 1 46 65 20 81	1 1 46 65 20 XX
S 16	PN 400	M 22 x 1.5	22	30	27	43	24.5	35	14	100	****	1 1 46 75 20 81	1 1 46 75 20 XX
S 20	PN 400	M 27 x 2	27	36	32	48	26.5	39	16	170	****	1 1 46 80 20 81	1 1 46 80 20 XX
S 25	PN 315	M 33 x 2	36	46	41	54	30	44	16	310	****	1 1 46 85 20 81	1 1 46 85 20 XX
S 30	PN 250	M 42 x 2	41	50	50	62	35.5	51	17	330	****	1 1 46 90 20 81	1 1 46 90 20 XX
S 38	PN 200	M 48 x 2	50	60	55	72	41	54	19	420	****	1 1 46 95 20 81	1 1 46 95 20 XX

Supplementary to Order No. for complete fitting tube connection	Supplementary to Order No.
2S	07
ES-4	09
BV-10	Refer to the front page

* Apply to complete fittings with 2S or ES-4 tube connection components.
For BV-10 Refer to the front page.

** With union nut and 2S, ES-4 or BV-10 tube connection components

*** Sample product code, see: LEE06LMOROMD

**** On request