

**AF25 Light CLASSIC**

Two row bar 50x50

Grid (A) 25, hole diameter 12,5mm

| Nr.   | B    | g     |
|-------|------|-------|
| 26617 | 50   | 108   |
| 25375 | 100  | 215   |
| 20426 | 150  | 323   |
| 20427 | 200  | 430   |
| 22949 | 250  | 538   |
| 20254 | 300  | 645   |
| 24246 | 350  | 753   |
| 20256 | 400  | 860   |
| 24248 | 450  | 968   |
| 22950 | 500  | 1.075 |
| 24249 | 550  | 1.183 |
| 24250 | 600  | 1.290 |
| 24247 | 650  | 1.398 |
| 24251 | 700  | 1.505 |
| 21824 | 750  | 1.613 |
| 28353 | 800  | 1.720 |
| 26842 | 850  | 1.828 |
| 24319 | 900  | 1.935 |
| 26841 | 950  | 2.043 |
| 22951 | 1000 | 2.150 |
| 27632 | 1050 | 2.258 |
| 27633 | 1100 | 2.365 |
| 26849 | 1150 | 2.437 |
| 25025 | 1200 | 2.580 |
| 21825 | 1250 | 2.688 |
| 27914 | 1300 | 2.795 |
| 28354 | 1350 | 2.903 |
| 27915 | 1400 | 3.010 |
| 24813 | 1450 | 3.118 |
| 22952 | 1500 | 3.225 |
| 27891 | 1600 | 3.440 |
| 33287 | 1700 | 3.655 |
| 33288 | 1800 | 3.870 |
| 33289 | 1900 | 4.085 |
| 21226 | 2000 | 4.300 |

**AF40 Light CLASSIC**

Two row bar 80x80

Grid (A) 40, hole diameter 20mm

| Nr.   | B    | g     |
|-------|------|-------|
| 24393 | 80   | 407   |
| 24940 | 120  | 610   |
| 23937 | 160  | 813   |
| 23938 | 200  | 1.017 |
| 24392 | 240  | 1.220 |
| 24825 | 280  | 1.423 |
| 24641 | 320  | 1.627 |
| 24809 | 360  | 1.830 |
| 23559 | 400  | 2.033 |
| 25922 | 440  | 2.237 |
| 24390 | 480  | 2.440 |
| 24808 | 520  | 2.643 |
| 24389 | 560  | 2.846 |
| 24451 | 600  | 3.050 |
| 24391 | 640  | 3.253 |
| 24454 | 680  | 3.456 |
| 24388 | 720  | 3.660 |
| 24826 | 760  | 3.863 |
| 23560 | 800  | 4.066 |
| 24629 | 840  | 4.270 |
| 26609 | 880  | 4.473 |
| 25095 | 920  | 4.676 |
| 25877 | 960  | 4.880 |
| 24624 | 1000 | 5.083 |
| 24807 | 1080 | 5.490 |
| 24943 | 1120 | 5.693 |
| 23561 | 1200 | 6.100 |
| 25317 | 1240 | 6.303 |
| 24806 | 1280 | 6.506 |
| 26003 | 1320 | 6.710 |
| 25094 | 1400 | 7.116 |
| 24630 | 1520 | 7.726 |
| 23562 | 1600 | 8.133 |
| 27202 | 1680 | 8.539 |
| 25629 | 1760 | 8.946 |

**AF50 Light CLASSIC**

Two row bar 100x100

Grid (A) 50, hole diameter 25mm

| Nr.   | B    | g      |
|-------|------|--------|
| 27569 | 100  | 839    |
| 28122 | 150  | 1.258  |
| 26735 | 200  | 1.678  |
| 27504 | 250  | 2.097  |
| 26821 | 300  | 2.516  |
| 27607 | 350  | 2.936  |
| 26786 | 400  | 3.355  |
| 26820 | 450  | 3.775  |
| 26787 | 500  | 4.194  |
| 26788 | 600  | 5.033  |
| 26818 | 700  | 5.872  |
| 27505 | 800  | 6.710  |
| 26789 | 900  | 7.549  |
| 26957 | 1000 | 8.388  |
| 27610 | 1100 | 9.227  |
| 27920 | 1200 | 10.066 |
| 27611 | 1300 | 10.904 |
| 27919 | 1400 | 11.743 |
| 26959 | 1500 | 12.582 |
| 27923 | 1600 | 13.421 |
| 30752 | 1700 | 14.260 |
| 27460 | 1800 | 15.098 |
| 30959 | 1900 | 15.937 |
| 26961 | 2000 | 16.767 |
| 26963 | 2500 | 20.970 |
| 26965 | 3000 | 25.164 |
| 26967 | 3500 | 29.358 |
| 26969 | 4000 | 33.552 |
| 26971 | 4500 | 37.746 |
| 26973 | 5000 | 41.940 |
| 26975 | 5500 | 46.134 |
| 26977 | 6000 | 50.328 |



**i** **ALUFIX CLASSIC** bars can be anodized in different colours. The colour natural is standard, black (-1) is available as an alternative. Other colours on request

**i** Other dimensions on request