

ALUFIX 40,
 Grid (A) 40, hole diameter 20mm

Nr.	A	B	C	D	g
20650	40	320	640	M10	22.118
20651	40	400	800	M10	34.560
20710	40	480	640	M10	33.177
20711	40	480	960	M10	49.766
20713	40	640	800	M10	55.296
20714	40	640	960	M10	66.355
20715	40	800	800	M10	69.120
20808	40	800	1600	M10	138.240
20809	40	960	960	M10	99.533
20810	40	960	1280	M10	132.710



Application examples of Alufix base plates and grid base plates

ALUFIX 50,
 Grid (A) 50, hole diameter 25mm

Nr.	A	B	C	D	g
28083	50	400	400	M12	21.600
28084	50	500	1000	M12	67.500
28085	50	600	800	M12	64.800
28086	50	600	1200	M12	97.200
28087	50	800	1000	M12	108.000
28088	50	800	1200	M12	129.600
28089	50	1000	1000	M12	135.000
28090	50	1000	2000	M12	270.000
28091	50	1200	1200	M12	194.400
28092	50	1200	1600	M12	259.200

