






★ 产品特点:加大了与安装部的摩擦,可起到防止松动的作用。



精度	类型		M 材质	S 表面处理
	B 尺寸固定型	B 尺寸指定型		
精密级	MWACG	MWACE	一般结构用钢	四氧化三铁保护膜
	MWBCEG	MWBCE		无电解镀锌
	MWECEG	MWECE	不锈钢	-

⚠ 如对防锈有要求, 请优先选用不锈钢材质或无电解镀锌产品。





金属垫圈 普通级 B 尺寸固定或指定

视角标准: 第一视角

① 代号

② D

③ Q

④ B

MWACG - D4 - Q2 - B1

B 尺寸固定型(精密级)

① 代号	② D		③ Q										④ B									
MWACG MWBCEG MWECEG	4	2											1	2								
	5	2	3											1	2							
	6	2	3	4											1	2						
			3	4											1.5							
	8	2	3	4	5	6						1	2	3	5							
			3	4	5	6						1.5										
	10	2	3	4	5	6	8						1	2	3	5						
			4	5	6	8						1.5										
	12		3	4	5	6	8	10						1	2	3	5					
				5	6	8	10						1.5									
	13		4	5	6	8	10						1	2	3	5						
				6	8						1.5											
	14		4	5	6	8	10						1	2	3	5						
				6	8	10						1.5										
	15		4	5	6	8	10	12						1	2	3	5					
				6	8	10	12						1.5									
	16		4	5	6	8	10	12						1	2	3	5					
				6	8	10	12						1.5									
	20		4	5	6	8	10	12	15	16						2	3	5				
				6	10	15						1.5										
25		6	8	10	12	15	16	20						2	3	5						
			8	10	12	15	16	20	25						2							
30			8	10	12	15	16	20	25						3							
				10	12	15	16	20	25	30						3						
35				10	12	15	16	20	25						3							
					10	12	15	16	20	25	30						3					
40					10	12	15	16	20	25	30						3					
						10	12	15	16	20	25	30						3				
50						10	12	15	16	20	25	30						3				
							10	12	15	16	20	25	30						3			
60							15	16	20	25	30						3					
								15	16	20	25	30						3				

① 代号

② D

③ Q

④ B

MWACE - D4 - Q2 - B1.0

B 尺寸指定型(普通级)

① 代号	② D		③ Q										④ B							
													指定单位0.5mm							
MWACE MWBCE MWECE	4	2																		
	5	2	3																	
	6	2	3	4																
	8	2	3	4	5	6														
	10	2	3	4	5	6	8													
	12		3	4	5	6	8	10												
	13		4	5	6	8	10													
	14		4	5	6	8	10						1.0 ~ 10.0							
	15		4	5	6	8	10	12												
	16		4	5	6	8	10	12												
	20		4	5	6	8	10	12	15	16										
	25			6	8	10	12	15	16	20										
	30				8	10	12	15	16	20	25									

交货期

1

天发货

数量分类	标准订单	特殊订单
	小单	大单
数量	1-200	201~
交货期	1 天发货	另行报价

⚠ 常州工厂发货。
⚠ 部分产品型号 7 天发货, 请以报价为准。