


Tuleja prowadząca samosmarująca

Self-lubricating guide bushing

TXG



Pierścień "Z" należy zamawiać osobno.
Ring "Z" must be ordered separately.

Mat: Brąz aluminiowy + grafit
Aluminium bronze + graphite

d	d1	d2	s	Z	t	L	NR KAT.	NR KAT.
9/10	14	16	3	Z14/14x1	5,5	12	TXG-09012	TXG-10012
					10,5	17	TXG-09017	TXG-10017
					15,5	22	TXG-09022	TXG-10022
					20,5	27	TXG-09027	TXG-10027
					29,5	36	TXG-09036	TXG-10036
					39,5	46	TXG-09046	TXG-10046
					49,5	56	TXG-09056	TXG-10056
12	18	23	6	Z18/18x1,2	7	17	TXG-12017	
					12	22	TXG-12022	
					17	27	TXG-12027	
					26	36	TXG-12036	
					36	46	TXG-12046	
					46	56	TXG-12056	
14/15	20	25	6	Z20/20x1,2	7	17	TXG-14017	TXG-15017
					12	22	TXG-14022	TXG-15022
					17	27	TXG-14027	TXG-15027
					26	36	TXG-14036	TXG-15036
					36	46	TXG-14046	TXG-15046
					46	56	TXG-14056	TXG-15056
16	22	27	6	Z22/22x1,2	12	22	TXG-16022	
					17	27	TXG-16027	
					26	36	TXG-16036	
					36	46	TXG-16046	
					46	56	TXG-16056	

Tuleja prowadząca samosmarująca

Self-lubricating guide bushing

TXG

d	d1	d2	s	Z	t	L	NR KAT.	NR KAT.
18/20	26	31	6	Z26/26x1,2	7	17	TXG-18017	TXG-20017
					12	22	TXG-18022	TXG-20022
					17	27	TXG-18027	TXG-20027
					26	36	TXG-18036	TXG-20036
					36	46	TXG-18046	TXG-20046
					46	56	TXG-18056	TXG-20056
					56	66	TXG-18066	TXG-20066
					66	76	TXG-18076	TXG-20076
22/24	30	35	6	Z30/30x1,5	11	22	TXG-22022	TXG-24022
					16	27	TXG-22027	TXG-24027
					25	36	TXG-22036	TXG-24036
					35	46	TXG-22046	TXG-24046
					45	56	TXG-22056	TXG-24056
					55	66	TXG-22066	TXG-24066
					65	76	TXG-22076	TXG-24076
					75	86	TXG-22086	TXG-24086
30/32	42	47	6	Z42/42x1,75	85	96	TXG-22096	TXG-24096
					14	27	TXG-30027	TXG-32027
					23	36	TXG-30036	TXG-32036
					33	46	TXG-30046	TXG-32046
					43	56	TXG-30056	TXG-32056
					53	66	TXG-30066	TXG-32066
					63	76	TXG-30076	TXG-32076
					73	86	TXG-30086	TXG-32086
					83	96	TXG-30096	TXG-32096
40/42	54	60	10	Z54/55x2,0	103	116	TXG-30116	TXG-32116
					28	46	TXG-40046	TXG-42046
					38	56	TXG-40056	TXG-42056
					48	66	TXG-40066	TXG-42066
					58	76	TXG-40076	TXG-42076
					68	86	TXG-40086	TXG-42086
					78	96	TXG-40096	TXG-42096
					98	116	TXG-40116	TXG-42116
					118	136	TXG-40136	TXG-42136