


# SPRING PLUNGER, WITH SPRING LOADED PIN, WITH SLOT, STANDARD SPRING FORCE

2472.01.



**2472.01. Spring plunger, with spring loaded pin, with slot, standard spring force**

Order No	d <sub>1</sub>	d <sub>2</sub>	l	s	SW	Spring force [N]	
						initial	final
2472.01.003	M3	1	12	1	0.7	2	4
2472.01.004	M4	1.5	15	1.5	1.3	4.5	16
2472.01.005	M5	2.4	18	2.3	1.5	6	19
2472.01.006	M6	2.7	20	2.5	2	6	19
2472.01.008	M8	3.5	22	3	2.5	10	39
2472.01.010	M10	4	22	3	3	10	39
2472.01.012	M12	6	28	4	4	12	53
2472.01.016	M16	7.5	32	5	5	45	100
2472.01.020	M20	10	40	7	6	52	125
2472.01.024	M24	12	52	10	8	70	170


**Material:**

Sleeve: Free machining steel, burnished  
 Pin: Free machining steel hardened, burnished  
 Spring: Nirosta

**Note:**

For locking and for pressing upwards or downwards. Removable with hexagon socket screw key or slotted screwdriver.

2472.31.



**2472.31. Spring plunger, with spring loaded pin, with slot, standard spring force**

Order No	d <sub>1</sub>	d <sub>2</sub>	l	s	SW	Spring force [N]	
						initial	final
2472.31.004	M4	1.5	15	1.5	1.3	4.5	16
2472.31.005	M5	2.4	18	2.3	1.5	6	19
2472.31.006	M6	2.7	20	2.5	2	6	19
2472.31.008	M8	3.5	22	3	2.5	10	39
2472.31.010	M10	4	22	3	3	10	39
2472.31.012	M12	6	28	4	4	12	53
2472.31.016	M16	7.5	32	5	5	45	100
2472.31.020	M20	10	40	7	6	52	125

**Material:**

Sleeve: Inox 1.4305  
 Pin: Inox 1.4305  
 Spring: Nirosta


**Note:**

For locking and for pressing upwards or downwards. Removable with hexagon socket screw key or slotted screwdriver.

# SPRING PLUNGER, WITH SPRING LOADED PIN, WITH SLOT, STANDARD SPRING FORCE



2472.21.



**Material:**

Sleeve: Free machining steel, burnished

Pin: Delrin white (POM)

Spring: Nirosta

**Note:**


For locking and for pressing upwards or downwards. Removable with hexagon socket screw key or slotted screwdriver.

**2472.21. Spring plunger, with spring loaded pin, with slot, standard spring force**

Order No	d <sub>1</sub>	d <sub>2</sub>	l	s	SW	Spring force [N]	
						initial	final
2472.21.004	M4	1.5	15	1.5	1.3	4.5	16
2472.21.005	M5	2.4	18	2.3	1.5	6	19
2472.21.006	M6	2.7	20	2.5	2	6	19
2472.21.008	M8	3.5	22	3	2.5	10	39
2472.21.010	M10	4	22	3	3	10	39
2472.21.012	M12	6	28	4	4	12	53
2472.21.016	M16	7.5	32	5	5	45	100



2472.22.



**Material:**

Sleeve: Nirosta 1.4305

Pin: Delrin white (POM)

Spring: Nirosta

**Note:**

For locking and for pressing upwards or downwards. Removable with hexagon socket screw key or slotted screwdriver.

**2472.22. Spring plunger, with spring loaded pin, with slot, standard spring force**

Order No	d <sub>1</sub>	d <sub>2</sub>	l	s	SW	Spring force [N]	
						initial	final
2472.22.004	M4	1.5	15	1.5	1.3	4.5	16
2472.22.005	M5	2.4	18	2.3	1.5	6	19
2472.22.006	M6	2.7	20	2.5	2	6	19
2472.22.008	M8	3.5	22	3	2.5	10	39
2472.22.010	M10	4	22	3	3	10	39
2472.22.012	M12	6	28	4	4	12	53
2472.22.016	M16	7.5	32	5	5	45	100