


Series E045 - split crossbar along the outer radius

Part No.	$B_i$ [mm]	$B_a$ [mm]	$R$ [mm]	Bending radii	Weight [kg/m]
E045.10. <input type="text"/> .0	10	16	<input type="text" value="018"/> <input type="text" value="028"/> <input type="text" value="038"/>		≈ 0,09
E045.16. <input type="text"/> .0	16	23	<input type="text" value="018"/> <input type="text" value="028"/> <input type="text" value="038"/>		≈ 0,11

$B_a$ : pin dimension approx. 0,1 - 0,3 mm wider!

Supplement Part No. with required radius. Example: E045.16.  .0

0 = standard color, other colors ► page 1.39 · Pitch = 13 mm/link - Links/m = 77




Series E045 - split crossbar along the outer radius with 2-chamber system

Part No.	$B_i$ [mm]	$B_a$ [mm]	$R$ [mm]	Bending radii	Weight [kg/m]
E045.2/7. <input type="text"/> .0	7 / 7	23	<input type="text" value="018"/> <input type="text" value="028"/> <input type="text" value="038"/>		≈ 0,13
E045.2/9. <input type="text"/> .0	9 / 9	27	<input type="text" value="018"/> <input type="text" value="028"/> <input type="text" value="038"/>		≈ 0,14

$B_a$ : pin dimension approx. 0,1 - 0,3 mm wider!

Supplement Part No. with required radius. Example: E045.2/9.  .0

0 = standard color, other colors ► page 1.39 · Pitch = 13 mm/link - Links/m = 77




Series E045 - split crossbar along the outer radius with 3-chamber system

Part No.	$B_i$ [mm]	$B_a$ [mm]	$R$ [mm]	Bending radii	Weight [kg/m]
E045.3/9. <input type="text"/> .0	9 / 9 / 9	37	<input type="text" value="018"/> <input type="text" value="028"/> <input type="text" value="038"/>		≈ 0,17

$B_a$ : pin dimension approx. 0,1 - 0,3 mm wider!

Supplement Part No. with required radius. Example: E045.3/9.  .0

0 = standard color, other colors ► page 1.39 · Pitch = 13 mm/link - Links/m = 77



Part No. structure

E045.	16.	<input type="text" value="038"/> .	<input type="text" value="0"/> .
-------	-----	------------------------------------	----------------------------------



Phone +49- (0) 22 03-96 49-800  
Fax +49- (0) 22 03-96 49-222

igus® GmbH  
51147 Cologne

Internet: [www.igus.eu](http://www.igus.eu)  
E-mail: [info@igus.de](mailto:info@igus.de)