


Sealing rings (seal-edge rings for banjo and gauge couplings)

- Sealing-edge ring for banjo couplings for external thread (DS)
- Sealing-edge ring for gauge couplings for internal thread (DM)



d2	d5	d6	h	Form	kg/100 ca.	Order-No.	Designation
M 8 x 1	8.1	12	2.5	DS	0.1	0080692100	GP-SR-M8B-H2,5
M 10 x 1	10.1	14	2.5	DS	0.1	0080702100	GP-SR-M10B-H2,5
M 12 x 1.5	12.1	17	3	DS	0.2	0080712100	GP-SR-M12B-H3
M 14 x 1.5	14.1	19	3	DS	0.2	0080722100	GP-SR-M14B-H3
M 16 x 1.5	16.1	21	3	DS	0.3	0080732100	GP-SR-M16B-H3
M 18 x 1.5	18.1	23	3	DS	0.3	0080742100	GP-SR-M18B-H3
M 20 x 1.5	20.1	25	3	DS	0.3	0080752100	GP-SR-M20B-H3
M 22 x 1.5	22.1	27	4.5	DS	0.6	0080142100	GP-SR-M22B-H4,5
M 26 x 1.5	26.15	31	3.5	DS	0.5	0080772100	GP-SR-M26B-H3,5
M 27 x 2	27.15	32	3.5	DS	0.5	0080782100	GP-SR-M27B-H3,5
M 33 x 2	33.15	39	3.5	DS	0.7	0080792100	GP-SR-M33B-H3,5
M 42 x 2	42.15	49	3.5	DS	1.0	0080802100	GP-SR-M42B-H3,5
M 48 x 2	48.15	55	3.5	DS	1.2	0080812100	GP-SR-M48B-H3,5
G 1/8 A	9.8	14	2.5	DS	0.1	0080822100	GP-SR-G1/8B-H3,5
G 1/4 A	5.8	11.2	4.6	DM	0.2	0080562100	GP-SR-IG1/4B-H4,6
G 1/4 A	13.3	18	3	DS	0.2	0080832100	GP-SR-G1/4B-H3
G 3/8 A	16.8	22	3	DS	0.3	0080842100	GP-SR-G3/8B-H3
G 1/2 A	11	18.3	5.2	DM	0.6	0080582100	GP-SR-IG1/2B-H5,2-C21
G 1/2 A	21.1	26	4.5	DS	0.5	0080852100	GP-SR-G1/2B-H4,5
G 3/4 A	26.6	32	3.5	DS	0.6	0080862100	GP-SR-G3/4B-H3,5
G 1 A	33.4	39	3.5	DS	0.7	0080872100	GP-SR-G1B-H3,5
G 1 1/4 A	42.1	49	3.5	DS	1.0	0080882100	GP-SR-G11/4B-H3,5
G 1 1/2 A	48	55	3.5	DS	1.2	0080892100	GP-SR-G11/2B-H3,5

Example for comp. :
DKA10X