

开口式固定环


内螺纹型



内螺纹型



类型		M 材质	S 表面处理	A 附件
细牙	粗牙			
SCABTM	SCABTU	一般结构用钢	四氧化三铁保护膜	1个内六角螺栓
SCAETM	SCAETU		无电解镀锌	1个内六角螺栓 (不锈钢)
SCANTM	SCANTU	不锈钢	-	



订购编号示例

① 代号 - ② Mm - ③ B
 SCABTM - M12 - B10

内螺纹型

① 代号	公称内径 ② Mm	③ B	Mm×P		D	M 粗牙	d	d ₁	a	T1		T2	T3
			(细牙螺纹)	(粗牙螺纹)						(细牙螺纹)	(粗牙螺纹)		
(细牙螺纹型) SCABTM SCAETM SCANTM	3	8	M3×0.35	M3×0.5	16	M3	3.4	6	1.0	4.5	4.5	2.2	3~5
	4		M4×0.5	M4×0.7	18					5	5	3	3.5~6
	5		M5×0.5	M5×0.8	20					5.5	5.5	4	5~6.5
	6	10	M6×0.75	M6×1.0	25	M4	4.5	7.5	1.5	6	6	4	6~6.5
	8		M8×0.75	M8×1.25						8	8		5
	8A		M8×1.0	-	-					-	9	10	
	10		M10×0.75	M10×1.5	30					9	-	9~10	
	10A		M10×1.0	-						10	10		
	10B		M10×1.25	-						11.5	-	6	10~11
	12		M12×1.0	M12×1.75	34					12	12.5		6
12A	M12×1.25	-	40	12.5		-	6	12~13					
(粗牙螺纹型) SCABTU SCAETU SCANTU	14	12	M14×1.5	-	34	M5	5.5	9	1.5	14	14	7	13
	16		M16×1.0	M16×2.0	11.5					12.5	8		14~15
	16A		M16×1.5	-	12					12.5		17	16
	18		M18×1.5	-	14					14		8	17~20
	20		M20×1.0	M20×2.5	17					17	10		18~20
	20A	M20×1.5	-	20	20								
	22	M22×1.5	-	55	M6	6.6	12	1.5	17	17	8	17~20	
	24	-	M24×3.0						20	20		10	18~20
	25	M25×1.5	-										
	27	M27×1.5	-										
30	M30×1.5	M30×3.5											

A3
固定环