

# ANACONDA IECEx-ATEX, RNA, IP66 / 68, NICKEL PLATED BRASS



## Anaconda IECEx-ATEX cable-hose-fitting type RNA & RAA, nickel plated brass.

Type RNA/RAA IECEx-ATEX approved nickel plated brass cable hose fittings are designed for use with Anaconda Sealite liquid tight conduits to connect and protect a **single unarmoured or armoured cable** (single core or multicore) in a potentially explosive atmosphere. A special designed connection set enables the fitting to be used with the Anaconda Multiflex range of uncovered conduits. Typical applications include motors, transformers, control equipment, Ex enclosures, terminal boxes, components etc., in the chemical and petrochemical, Oil & Gas, bulk handling, wood processing and food and pharma industries. In case a 45° or 90° solution is needed it is possible to use the IECEx-ATEX Anaconda adapter type RNC in combination with a 45° or 90° Anaconda nickel plated brass swivel fitting.

### Material & Construction:

**Construction:** Nickel plated brass fitting, consisting of 7 parts (counter nut, clamping ring, ferrule, intermediate housing, pressure ring, sealing rubber and body). Also available as barrier version with sealing resin.

**Material:** Counter nut, intermediate housing, pressure ring and body are nickel plated brass. Ferrule is from galvanized steel, sealing rubber is from EPDM rubber, clamping ring is from PA6.

Also available in stainless steel AISI-316.

Fittings are fully RoHS compliant.

**Temperature:** -40 °C till +100 °C continuous. With silicone sealing rubber -65 °C till +220 °C continuous.


**Protection class:** IP67 on the conduit and standard IP66 between body and switchbox, with a flat seal between body and switchbox IP68.

**Colour:** Metal.

For unarmoured cable, IECEx-ATEX certified and marked;  
▲ RCN (type) (threadsize) IECEx INE 10.0010X Ex d/e I Mb IIC Gb Ex tb IIIC Db  
⚡ CE INERIS 06ATEX0014X I M2 / II 2 GD, IP66 / IP68 EAC

RNA, ISO, IECEx-ATEX cable-hose-fitting, nickel plated brass, EPDM seal.

(-40 °C till +100 °C)




Thread	Sealite Size (Inch)	Clamping Range (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	E	F			
M16 x 1,5	5/16"	4 - 7	71	15	26	25	24	10	822.006.0	10,8
M20 x 1,5	5/16"	4 - 7	71	15	26	25	24	10	822.007.0	10,8
M16 x 1,5	3/8"	4 - 7	71	15	26	25	24	10	822.010.0	10,8
M16 x 1,5	3/8"	7 - 10	71	15	26	25	24	10	822.011.0	10,8
M20 x 1,5	3/8"	4 - 7	71	15	26	25	24	10	822.008.0	10,8
M20 x 1,5	3/8"	7 - 10	71	15	26	25	24	10	822.009.0	10,8
M20 x 1,5	1/2"	5,5 - 8	74	15	30	32	30	10	822.012.0	17,8
M20 x 1,5	1/2"	8 - 10,5	74	15	30	32	30	10	822.013.0	17,8
M20 x 1,5	1/2"	10,5 - 13	74	15	30	32	30	10	822.014.0	17,8
M25 x 1,5	3/4"	10,5 - 13	74	15	35	36	35	5	822.015.0	21,6
M25 x 1,5	3/4"	13 - 15,5	74	15	35	36	35	5	822.018.0	21,6
M25 x 1,5	3/4"	15,5 - 18	74	15	35	36	35	5	822.019.0	21,6
M32 x 1,5	1"	15 - 18	90	15	45	45	42	5	822.023.0	38,0
M32 x 1,5	1"	18 - 21	90	15	45	45	42	5	822.024.0	38,0
M32 x 1,5	1"	21 - 23,5	90	15	45	45	42	5	822.025.0	38,0
M40 x 1,5	1.1/4"	21 - 24	94	15	55	55	48	2	822.029.0	45,1
M40 x 1,5	1.1/4"	24 - 27	94	15	55	55	48	2	822.030.0	45,1
M40 x 1,5	1.1/4"	27 - 30	94	15	55	55	48	2	822.031.0	45,1

# ANACONDA IECEx-ATEX, RNA, IP66 / 68, NICKEL PLATED BRASS


For unarmoured cable, IECEx-ATEX certified and marked;  
 ▲ RCN (type) (threadsize) IECEx INE 10.0010X Ex d/e I Mb IIC Gb Ex tb IIIC Db  
 Ex CE INERIS 06ATEX0014X I M2 / II 2 GD, IP66 / IP68 EAC

RNA, NPT, IECEx-ATEX cable-hose-fitting, nickel plated  
 brass, EPDM seal. (-40 °C till +100 °C)




Thread	Sealtite Size (Inch)	Clamping Range (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	E	F			
NPT 1/2"	3/8"	4 - 7	74	18	26	25	24	10	824.010.0	10,8
NPT 1/2"	3/8"	7 - 10	74	18	26	25	24	10	824.011.0	10,8
NPT 1/2"	1/2"	5,5 - 8	77	18	30	32	30	10	824.012.0	17,8
NPT 1/2"	1/2"	8 - 10,5	77	18	30	32	30	10	824.013.0	17,8
NPT 1/2"	1/2"	10,5 - 13	77	18	30	32	30	10	824.014.0	17,8
NPT 3/4"	3/4"	10,5 - 13	77	18	35	36	35	5	824.015.0	21,6
NPT 3/4"	3/4"	13 - 15,5	77	18	35	36	35	5	824.018.0	21,6
NPT 3/4"	3/4"	15,5 - 18	77	18	35	36	35	5	824.019.0	21,6
NPT 1"	1"	15 - 18	97	22	45	45	42	5	824.023.0	38,0
NPT 1"	1"	18 - 21	97	22	45	45	42	5	824.024.0	38,0
NPT 1"	1"	21 - 23,5	97	22	45	45	42	5	824.025.0	38,0

RNA, ISO, IECEx-ATEX cable-hose-fitting, nickel plated  
 brass, Silicone seal. (-65 °C till +220 °C)



Thread	Sealtite Size (Inch)	Clamping Range (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	E	F			
M16 x 1,5	3/8"	6 - 8	71	15	26	25	24	10	822.010.3	10,8
M16 x 1,5	3/8"	8 - 10	71	15	26	25	24	10	822.011.3	10,8
M20 x 1,5	3/8"	8 - 10	71	15	26	25	24	10	822.009.3	10,8
M20 x 1,5	1/2"	5,5 - 8	74	15	30	32	30	10	822.012.3	17,8
M20 x 1,5	1/2"	8 - 10,5	74	15	30	32	30	10	822.013.3	17,8
M20 x 1,5	1/2"	10,5 - 13	74	15	30	32	30	10	822.014.3	17,8
M25 x 1,5	3/4"	10,5 - 13	74	15	35	36	35	5	822.015.3	21,6
M25 x 1,5	3/4"	13 - 15,5	74	15	35	36	35	5	822.018.3	21,6
M25 x 1,5	3/4"	15,5 - 18	74	15	35	36	35	5	822.019.3	21,6
M32 x 1,5	1"	15 - 18	90	15	45	45	42	5	822.023.3	38,0
M32 x 1,5	1"	18 - 21	90	15	45	45	42	5	822.024.3	38,0
M32 x 1,5	1"	21 - 23,5	90	15	45	45	42	5	822.025.3	38,0
M40 x 1,5	1.1/4"	21 - 24	94	15	55	55	48	2	822.029.3	45,1
M40 x 1,5	1.1/4"	24 - 27	94	15	55	55	48	2	822.030.3	45,1
M40 x 1,5	1.1/4"	27 - 30	94	15	55	55	48	2	822.031.3	45,1

RNA, NPT, IECEx-ATEX cable-hose-fitting, nickel plated  
 brass, Silicone seal. (-65 °C till +220 °C)




Thread	Sealtite Size (Inch)	Clamping Range (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	E	F			
NPT 1/2"	3/8"	6 - 8	74	18	26	25	24	10	824.010.3	10,8
NPT 1/2"	3/8"	8 - 10	74	18	26	25	24	10	824.011.3	10,8
NPT 1/2"	1/2"	5,5 - 8	77	18	30	32	30	10	824.012.3	17,8
NPT 1/2"	1/2"	8 - 10,5	77	18	30	32	30	10	824.013.3	17,8
NPT 1/2"	1/2"	10,5 - 13	77	18	30	32	30	10	824.014.3	17,8
NPT 3/4"	3/4"	10,5 - 13	77	18	35	36	35	5	824.015.3	21,6
NPT 3/4"	3/4"	13 - 15,5	77	18	35	36	35	5	824.018.3	21,6
NPT 3/4"	3/4"	15,5 - 18	77	18	35	36	35	5	824.019.3	21,6
NPT 1"	1"	15 - 18	97	22	45	45	42	5	824.023.3	38,0
NPT 1"	1"	18 - 21	97	22	45	45	42	5	824.024.3	38,0
NPT 1"	1"	21 - 23,5	97	22	45	45	42	5	824.025.3	38,0

Company  
 Anaconda Multiflex  
 Anaconda Multitite  
 Anaconda Sealtite  
 Anaconda Sealtite Spec.  
 Anaconda Fittings  
 Anaconda Accessories  
 Anaconda IECEx - ATEX

# ANACONDA IECEx-ATEX, RAA, IP66 / 68, NICKEL PLATED BRASS


For armoured cable, IECEx-ATEX certified and marked;  
 ▲ RCN (type) (threadsize) IECEx INE 10.0010X Ex d/e I Mb IIC Gb Ex tb IIIC Db  
 ⚡ CE INERIS 06ATEX0014X I M2 / II 2 GD, IP66 / IP68 EAC

RAA, ISO, IECEx-ATEX EMC cable-hose-fitting,  
 nickel plated brass, EPDM seal. (-40 °C till +100 °C)



Thread	Sealrite Size (Inch)	Clamping Range (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	E	F			
M16 x 1,5	5/16"	4 - 7	71	15	26	25	24	10	822.206.0	10,8
M20 x 1,5	5/16"	4 - 7	71	15	26	25	24	10	822.207.0	10,8
M16 x 1,5	3/8"	4 - 7	71	15	26	25	24	10	822.210.0	10,8
M16 x 1,5	3/8"	7 - 10	71	15	26	25	24	10	822.211.0	10,8
M20 x 1,5	3/8"	7 - 10	71	15	26	25	24	10	822.209.0	10,8
M20 x 1,5	1/2"	5,5 - 8	74	15	30	32	30	10	822.212.0	17,8
M20 x 1,5	1/2"	8 - 10,5	74	15	30	32	30	10	822.213.0	17,8
M20 x 1,5	1/2"	10,5 - 13	74	15	30	32	30	10	822.214.0	17,8
M25 x 1,5	3/4"	10,5 - 13	74	15	35	36	35	5	822.215.0	21,6
M25 x 1,5	3/4"	13 - 15,5	74	15	35	36	35	5	822.218.0	21,6
M25 x 1,5	3/4"	15,5 - 18	74	15	35	36	35	5	822.219.0	21,6
M32 x 1,5	1"	15 - 18	90	15	45	45	42	5	822.223.0	38,0
M32 x 1,5	1"	18 - 21	90	15	45	45	42	5	822.224.0	38,0
M32 x 1,5	1"	21 - 23,5	90	15	45	45	42	5	822.225.0	38,0
M40 x 1,5	1.1/4"	21 - 24	94	15	55	55	48	2	822.229.0	45,1
M40 x 1,5	1.1/4"	24 - 27	94	15	55	55	48	2	822.230.0	45,1
M40 x 1,5	1.1/4"	27 - 30	94	15	55	55	48	2	822.231.0	45,1


RAA, NPT, IECEx-ATEX EMC cable-hose-fitting,  
 nickel plated brass, EPDM seal. (-40 °C till +100 °C)



Thread	Sealrite Size (Inch)	Clamping Range (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	E	F			
NPT 1/2"	3/8"	4 - 7	74	18	26	25	24	10	824.210.0	10,8
NPT 1/2"	3/8"	7 - 10	74	18	26	25	24	10	824.211.0	10,8
NPT 1/2"	1/2"	5,5 - 8	77	18	30	32	30	10	824.212.0	17,8
NPT 1/2"	1/2"	8 - 10,5	77	18	30	32	30	10	824.213.0	17,8
NPT 1/2"	1/2"	10,5 - 13	77	18	30	32	30	10	824.214.0	17,8
NPT 3/4"	3/4"	10,5 - 13	77	18	35	36	35	5	824.215.0	21,6
NPT 3/4"	3/4"	13 - 15,5	77	18	35	36	35	5	824.218.0	21,6
NPT 3/4"	3/4"	15,5 - 18	77	18	35	36	35	5	824.219.0	21,6
NPT 1"	1"	15 - 18	97	22	45	45	42	5	824.223.0	38,0
NPT 1"	1"	18 - 21	97	22	45	45	42	5	824.224.0	38,0
NPT 1"	1"	21 - 23,5	97	22	45	45	42	5	824.225.0	38,0

# ANACONDA IECEX-ATEX, RAA, IP66 / 68, NICKEL PLATED BRASS


For armoured cable, IECEX-ATEX certified and marked;  
 ▲ RCN (type) (threadsize) IECEX INE 10.0010X Ex d/e I Mb IIC Gb Ex tb IIIC Db  
 ⚡ CE INERIS 06ATEX0014X I M2 / II 2 GD, IP66 / IP68 EAC



RAA, ISO, IECEX-ATEX EMC cable-hose-fitting,  
 nickel plated brass, Silicone seal. (-65 °C till +220 °C)



Thread	Sealtite	Clamping	Dimensions in mm					Standard	Article	Weight
			ISO	Size (Inch)	Range (mm)	A	B			
M16 x 1,5	3/8"	6 - 8	71	15	26	25	24	10	822.210.3	10,8
M16 x 1,5	3/8"	8 - 10	71	15	26	25	24	10	822.211.3	10,8
M20 x 1,5	3/8"	8 - 10	71	15	26	25	24	10	822.209.3	10,8
M20 x 1,5	1/2"	5,5 - 8	74	15	30	32	30	10	822.212.3	17,8
M20 x 1,5	1/2"	8 - 10,5	74	15	30	32	30	10	822.213.3	17,8
M20 x 1,5	1/2"	10,5 - 13	74	15	30	32	30	10	822.214.3	17,8
M25 x 1,5	3/4"	10,5 - 13	74	15	35	36	35	5	822.215.3	21,6
M25 x 1,5	3/4"	13 - 15,5	74	15	35	36	35	5	822.218.3	21,6
M25 x 1,5	3/4"	15,5 - 18	74	15	35	36	35	5	822.219.3	21,6
M32 x 1,5	1"	15 - 18	90	15	45	45	42	5	822.223.3	38,0
M32 x 1,5	1"	18 - 21	90	15	45	45	42	5	822.224.3	38,0
M32 x 1,5	1"	21 - 23,5	90	15	45	45	42	5	822.225.3	38,0
M40 x 1,5	1.1/4"	21 - 24	94	15	55	55	48	2	822.229.3	45,1
M40 x 1,5	1.1/4"	24 - 27	94	15	55	55	48	2	822.230.3	45,1
M40 x 1,5	1.1/4"	27 - 30	94	15	55	55	48	2	822.231.3	45,1



RAA, NPT, IECEX-ATEX EMC cable-hose-fitting,  
 nickel plated brass, Silicone seal. (-65 °C till +220 °C)



Thread	Sealtite	Clamping	Dimensions in mm					Standard	Article	Weight
			NPT	Size (Inch)	Range (mm)	A	B			
NPT 1/2"	3/8"	6 - 8	74	18	26	25	24	10	824.210.3	10,8
NPT 1/2"	3/8"	8 - 10	74	18	26	25	24	10	824.211.3	10,8
NPT 1/2"	1/2"	5,5 - 8	77	18	30	32	30	10	824.212.3	17,8
NPT 1/2"	1/2"	8 - 10,5	77	18	30	32	30	10	824.213.3	17,8
NPT 1/2"	1/2"	10,5 - 13	77	18	30	32	30	10	824.214.3	17,8
NPT 3/4"	3/4"	10,5 - 13	77	18	35	36	35	5	824.215.3	21,6
NPT 3/4"	3/4"	13 - 15,5	77	18	35	36	35	5	824.218.3	21,6
NPT 3/4"	3/4"	15,5 - 18	77	18	35	36	35	5	824.219.3	21,6
NPT 1"	1"	15 - 18	97	22	45	45	42	5	824.223.3	38,0
NPT 1"	1"	18 - 21	97	22	45	45	42	5	824.224.3	38,0
NPT 1"	1"	21 - 23,5	97	22	45	45	42	5	824.225.3	38,0

Company  
 Anaconda Multiflex  
 Anaconda Multitite  
 Anaconda Sealtite  
 Anaconda Sealtite Spec.  
 Anaconda Fittings  
 Anaconda Accessories  
 Anaconda IECEX - ATEX

# ANACONDA IECEx-ATEX, RNA-316, IP66 / 68, STAINLESS STEEL



## Anaconda IECEx-ATEX cable-hose-fitting type RNA-316 & RAA-316, stainless steel.

Types RNA/RAA IECEx-ATEX approved stainless steel type cable hose fittings are designed for use with Anaconda Sealite liquid tight conduits to connect and protect a **single unarmoured or armoured cable** (single core or multicore) in a potentially explosive atmosphere. The use of stainless steel AISI-316 material ensures good resistance to corrosive chemicals. A special designed connection set enables the fitting to be used with the Anaconda Multiflex range of uncovered conduits. Typical applications include motors, transformers, control equipment, Ex enclosures, terminal boxes, components etc., in the chemical and petrochemical, Oil & Gas, bulk handling, wood processing and food and pharma industries.

In case a 45° or 90° solution is needed it is possible to use the IECEx-ATEX Anaconda adapter type RNC-316 in combination with a 45° or 90° Anaconda stainless steel swivel fitting.

### Material & Construction:

**Construction:** Stainless steel AISI-316 fitting, consisting of 7 parts (counter nut, clamping ring, ferrule, intermediate housing, pressure ring, sealing rubber and body).

Also available as barrier version with sealing resin.

**Material:** Counter nut, intermediate housing and body are stainless steel AISI-316. Ferrule and pressure ring are nickel plated brass. Sealing rubber is from EPDM rubber, clamping ring is from PA6.

Fittings are fully RoHS compliant.

**Temperature:** -40 °C till +100 °C continuous. With silicone sealing rubber -65 °C till +220 °C continuous.


**Protection class:** IP67 on the conduit and standard IP66 between body and switchbox, with a flat seal between body and switchbox IP68.

**Colour:** Metal.

For unarmoured cable, IECEx-ATEX certified and marked;  
▲ RCN (type) (threadsize) IECEx INE 10.0010X Ex d/e I Mb IIC Gb Ex tb IIIC Db  
Ⓢ CE INERIS 06ATEX0014X I M2 / II 2 GD, IP66 / IP68 EAC

RNA-316, ISO, IECEx-ATEX cable-hose-fitting, stainless steel AISI-316, EPDM seal.

(-40 °C till +100 °C)




Thread	Sealite Size (Inch)	Clamping Range (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	E	F			
M16 x 1,5	5/16"	4 - 7	71	15	26	25	24	10	822.006.9	10,8
M20 x 1,5	5/16"	4 - 7	71	15	26	25	24	10	822.007.9	10,8
M16 x 1,5	3/8"	4 - 7	71	15	26	25	24	10	822.010.9	10,8
M16 x 1,5	3/8"	7 - 10	71	15	26	25	24	10	822.011.9	10,8
M20 x 1,5	3/8"	4 - 7	71	15	26	25	24	10	822.008.9	10,8
M20 x 1,5	3/8"	7 - 10	71	15	26	25	24	10	822.009.9	10,8
M20 x 1,5	1/2"	5,5 - 8	74	15	30	32	30	10	822.012.9	17,8
M20 x 1,5	1/2"	8 - 10,5	74	15	30	32	30	10	822.013.9	17,8
M20 x 1,5	1/2"	10,5 - 13	74	15	30	32	30	10	822.014.9	17,8
M25 x 1,5	3/4"	10,5 - 13	74	15	35	36	36	5	822.015.9	21,6
M25 x 1,5	3/4"	13 - 15,5	74	15	35	36	36	5	822.018.9	21,6
M25 x 1,5	3/4"	15,5 - 18	74	15	35	36	36	5	822.019.9	21,6
M32 x 1,5	1"	15 - 18	90	15	45	45	42	5	822.023.9	38,0
M32 x 1,5	1"	18 - 21	90	15	45	45	42	5	822.024.9	38,0
M32 x 1,5	1"	21 - 23,5	90	15	45	45	42	5	822.025.9	38,0
M40 x 1,5	1.1/4"	21 - 24	94	15	55	55	48	2	822.029.9	45,1
M40 x 1,5	1.1/4"	24 - 27	94	15	55	55	48	2	822.030.9	45,1
M40 x 1,5	1.1/4"	27 - 30	94	15	55	55	48	2	822.031.9	45,1

# ANACONDA IECEx-ATEX, RNA-316, IP66 / 68, STAINLESS STEEL


For unarmoured cable, IECEx-ATEX certified and marked;  
▲ RCN (type) (threadsize) IECEx INE 10.0010X Ex d/e I Mb IIC Gb Ex tb IIIC Db  
▲ CE INERIS 06ATEX0014X I M2 / II 2 GD, IP66 / IP68 EAC

RNA-316, NPT, IECEx-ATEX cable-hose-fitting, stainless steel AISI-316, EPDM seal. (-40 °C till +100 °C)




Thread NPT	Sealtite Size (Inch)	Clamping Range (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	E	F			
NPT 1/2"	3/8"	4 - 7	74	18	26	25	24	10	824.010.9	10,8
NPT 1/2"	3/8"	7 - 10	74	18	26	25	24	10	824.011.9	10,8
NPT 1/2"	1/2"	5,5 - 8	77	18	30	32	30	10	824.012.9	17,8
NPT 1/2"	1/2"	8 - 10,5	77	18	30	32	30	10	824.013.9	17,8
NPT 1/2"	1/2"	10,5 - 13	77	18	30	32	30	10	824.014.9	17,8
NPT 3/4"	3/4"	10,5 - 13	77	18	35	36	36	5	824.015.9	21,6
NPT 3/4"	3/4"	13 - 15,5	77	18	35	36	36	5	824.018.9	21,6
NPT 3/4"	3/4"	15,5 - 18	77	18	35	36	36	5	824.019.9	21,6
NPT 1"	1"	15 - 18	97	22	45	45	42	5	824.023.9	38,0
NPT 1"	1"	18 - 21	97	22	45	45	42	5	824.024.9	38,0
NPT 1"	1"	21 - 23,5	97	22	45	45	42	5	824.025.9	38,0

RNA-316, ISO, IECEx-ATEX cable-hose-fitting, stainless steel AISI-316, Silicone seal. (-65 °C till +220 °C)



Thread ISO	Sealtite Size (Inch)	Clamping Range (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	E	F			
M16 x 1,5	3/8"	6 - 8	71	15	26	25	24	10	822.010.6	10,8
M16 x 1,5	3/8"	8 - 10	71	15	26	25	24	10	822.011.6	10,8
M20 x 1,5	3/8"	8 - 10	71	15	26	25	24	10	822.009.6	10,8
M20 x 1,5	1/2"	5,5 - 8	74	15	30	32	30	10	822.012.6	17,8
M20 x 1,5	1/2"	8 - 10,5	74	15	30	32	30	10	822.013.6	17,8
M20 x 1,5	1/2"	10,5 - 13	74	15	30	32	30	10	822.014.6	17,8
M25 x 1,5	3/4"	10,5 - 13	74	15	35	36	36	5	822.015.6	21,6
M25 x 1,5	3/4"	13 - 15,5	74	15	35	36	36	5	822.018.6	21,6
M25 x 1,5	3/4"	15,5 - 18	74	15	35	36	36	5	822.019.6	21,6
M32 x 1,5	1"	15 - 18	90	15	45	45	42	5	822.023.6	38,0
M32 x 1,5	1"	18 - 21	90	15	45	45	42	5	822.024.6	38,0
M32 x 1,5	1"	21 - 23,5	90	15	45	45	42	5	822.025.6	38,0
M40 x 1,5	1.1/4"	21 - 24	94	15	55	55	48	2	822.029.6	45,1
M40 x 1,5	1.1/4"	24 - 27	94	15	55	55	48	2	822.030.6	45,1
M40 x 1,5	1.1/4"	27 - 30	94	15	55	55	48	2	822.031.6	45,1

RNA-316, NPT, IECEx-ATEX cable-hose-fitting, stainless steel AISI-316, Silicone seal. (-65 °C till +220 °C)




Thread NPT	Sealtite Size (Inch)	Clamping Range (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	E	F			
NPT 1/2"	3/8"	6 - 8	74	18	26	25	24	10	824.010.6	10,8
NPT 1/2"	3/8"	8 - 10	74	18	26	25	24	10	824.011.6	10,8
NPT 1/2"	1/2"	5,5 - 8	77	18	30	32	30	10	824.012.6	17,8
NPT 1/2"	1/2"	8 - 10,5	77	18	30	32	30	10	824.013.6	17,8
NPT 1/2"	1/2"	10,5 - 13	77	18	30	32	30	10	824.014.6	17,8
NPT 3/4"	3/4"	10,5 - 13	77	18	35	36	36	5	824.015.6	21,6
NPT 3/4"	3/4"	13 - 15,5	77	18	35	36	36	5	824.018.6	21,6
NPT 3/4"	3/4"	15,5 - 18	77	18	35	36	36	5	824.019.6	21,6
NPT 1"	1"	15 - 18	97	22	45	45	42	5	824.023.6	38,0
NPT 1"	1"	18 - 21	97	22	45	45	42	5	824.024.6	38,0
NPT 1"	1"	21 - 23,5	97	22	45	45	42	5	824.025.6	38,0

Company  
Anaconda Multiflex  
Anaconda Multitite  
Anaconda Sealtite  
Anaconda Sealtite Spec.  
Anaconda Fittings  
Anaconda Accessories  
Anaconda IECEx - ATEX

# ANACONDA IECEx-ATEX, RAA-316, IP66 / 68, STAINLESS STEEL


For armoured cable, IECEx-ATEX certified and marked;  
 ▲ RCN (type) (threadsize) IECEx INE 10.0010X Ex d/e I Mb IIC Gb Ex tb IIIC Db  
 ⚡ CE INERIS 06ATEX0014X I M2 / II 2 GD, IP66 / IP68 EAC

RAA-316, ISO, IECEx-ATEX EMC cable-hose-fitting, stainless steel AISI-316, EPDM seal. (-40 °C till +100 °C)



Thread	Sealrite Size (Inch)	Clamping Range (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	E	F			
M16 x 1,5	5/16"	4 - 7	71	15	26	25	24	10	822.206.9	10,8
M20 x 1,5	5/16"	4 - 7	71	15	26	25	24	10	822.207.9	10,8
M16 x 1,5	3/8"	4 - 7	71	15	26	25	24	10	822.210.9	10,8
M16 x 1,5	3/8"	7 - 10	71	15	26	25	24	10	822.211.9	10,8
M20 x 1,5	3/8"	7 - 10	71	15	26	25	24	10	822.209.9	10,8
M20 x 1,5	1/2"	5,5 - 8	74	15	30	32	30	10	822.212.9	17,8
M20 x 1,5	1/2"	8 - 10,5	74	15	30	32	30	10	822.213.9	17,8
M20 x 1,5	1/2"	10,5 - 13	74	15	30	32	30	10	822.214.9	17,8
M25 x 1,5	3/4"	10,5 - 13	74	15	35	36	36	5	822.215.9	21,6
M25 x 1,5	3/4"	13 - 15,5	74	15	35	36	36	5	822.218.9	21,6
M25 x 1,5	3/4"	15,5 - 18	74	15	35	36	36	5	822.219.9	21,6
M32 x 1,5	1"	15 - 18	90	15	45	45	42	5	822.223.9	38,0
M32 x 1,5	1"	18 - 21	90	15	45	45	42	5	822.224.9	38,0
M32 x 1,5	1"	21 - 23,5	90	15	45	45	42	5	822.225.9	38,0
M40 x 1,5	1.1/4"	21 - 24	94	15	55	55	48	2	822.229.9	45,1
M40 x 1,5	1.1/4"	24 - 27	94	15	55	55	48	2	822.230.9	45,1
M40 x 1,5	1.1/4"	27 - 30	94	15	55	55	48	2	822.231.9	45,1


RAA-316, NPT, IECEx-ATEX EMC cable-hose-fitting, stainless steel AISI-316, EPDM seal. (-40 °C till +100 °C)



Thread	Sealrite Size (Inch)	Clamping Range (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	E	F			
NPT 1/2"	3/8"	4 - 7	74	18	26	25	24	10	824.210.9	10,8
NPT 1/2"	3/8"	7 - 10	74	18	26	25	24	10	824.211.9	10,8
NPT 1/2"	1/2"	5,5 - 8	77	18	30	32	30	10	824.212.9	17,8
NPT 1/2"	1/2"	8 - 10,5	77	18	30	32	30	10	824.213.9	17,8
NPT 1/2"	1/2"	10,5 - 13	77	18	30	32	30	10	824.214.9	17,8
NPT 3/4"	3/4"	10,5 - 13	77	18	35	36	36	5	824.215.9	21,6
NPT 3/4"	3/4"	13 - 15,5	77	18	35	36	36	5	824.218.9	21,6
NPT 3/4"	3/4"	15,5 - 18	77	18	35	36	36	5	824.219.9	21,6
NPT 1"	1"	15 - 18	97	22	45	45	42	5	824.223.9	38,0
NPT 1"	1"	18 - 21	97	22	45	45	42	5	824.224.9	38,0
NPT 1"	1"	21 - 23,5	97	22	45	45	42	5	824.225.9	38,0

# ANACONDA IECEX-ATEX, RAA-316, IP66 / 68, STAINLESS STEEL


For armoured cable, IECEX-ATEX certified and marked;  
 ▲ RCN (type) (threadsize) IECEX INE 10.0010X Ex d/e I Mb IIC Gb Ex tb IIIC Db  
 ⚡ CE INERIS 06ATEX0014X I M2 / II 2 GD, IP66 / IP68 EAC



RAA-316, ISO, IECEX-ATEX EMC cable-hose-fitting, stainless steel AISI-316, Silicone seal. (-65 °C till +220 °C)



Thread	Sealtite	Clamping	Dimensions in mm					Standard	Article	Weight
			ISO	Size (Inch)	Range (mm)	A	B			
M16 x 1,5	3/8"	6 - 8	71	15	26	25	24	10	822.210.6	10,8
M16 x 1,5	3/8"	8 - 10	71	15	26	25	24	10	822.211.6	10,8
M20 x 1,5	3/8"	8 - 10	71	15	26	25	24	10	822.209.6	10,8
M20 x 1,5	1/2"	5,5 - 8	74	15	30	32	30	10	822.212.6	17,8
M20 x 1,5	1/2"	8 - 10,5	74	15	30	32	30	10	822.213.6	17,8
M20 x 1,5	1/2"	10,5 - 13	74	15	30	32	30	10	822.214.6	17,8
M25 x 1,5	3/4"	10,5 - 13	74	15	35	36	36	5	822.215.6	21,6
M25 x 1,5	3/4"	13 - 15,5	74	15	35	36	36	5	822.218.6	21,6
M25 x 1,5	3/4"	15,5 - 18	74	15	35	36	36	5	822.219.6	21,6
M32 x 1,5	1"	15 - 18	90	15	45	45	42	5	822.223.6	38,0
M32 x 1,5	1"	18 - 21	90	15	45	45	42	5	822.224.6	38,0
M32 x 1,5	1"	21 - 23,5	90	15	45	45	42	5	822.225.6	38,0
M40 x 1,5	1.1/4"	21 - 24	94	15	55	55	48	2	822.229.6	45,1
M40 x 1,5	1.1/4"	24 - 27	94	15	55	55	48	2	822.230.6	45,1
M40 x 1,5	1.1/4"	27 - 30	94	15	55	55	48	2	822.231.6	45,1



RAA-316, NPT, IECEX-ATEX EMC cable-hose-fitting, stainless steel AISI-316, Silicone seal. (-65 °C till +220 °C)



Thread	Sealtite	Clamping	Dimensions in mm					Standard	Article	Weight
			NPT	Size (Inch)	Range (mm)	A	B			
NPT 1/2"	3/8"	6 - 8	74	18	26	25	24	10	824.210.6	10,8
NPT 1/2"	3/8"	8 - 10	74	18	26	25	24	10	824.211.6	10,8
NPT 1/2"	1/2"	5,5 - 8	77	18	30	32	30	10	824.212.6	17,8
NPT 1/2"	1/2"	8 - 10,5	77	18	30	32	30	10	824.213.6	17,8
NPT 1/2"	1/2"	10,5 - 13	77	18	30	32	30	10	824.214.6	17,8
NPT 3/4"	3/4"	10,5 - 13	77	18	35	36	36	5	824.215.6	21,6
NPT 3/4"	3/4"	13 - 15,5	77	18	35	36	36	5	824.218.6	21,6
NPT 3/4"	3/4"	15,5 - 18	77	18	35	36	36	5	824.219.6	21,6
NPT 1"	1"	15 - 18	97	22	45	45	42	5	824.223.6	38,0
NPT 1"	1"	18 - 21	97	22	45	45	42	5	824.224.6	38,0
NPT 1"	1"	21 - 23,5	97	22	45	45	42	5	824.225.6	38,0

Company  
 Anaconda Multiflex  
 Anaconda Multitite  
 Anaconda Sealtite  
 Anaconda Sealtite Spec.  
 Anaconda Fittings  
 Anaconda Accessories  
 Anaconda IECEX - ATEX