


# 电机支座

## 整合型传动座·宽型

■宽型




CAD  
2D 3D

①代号	类型		M 材质	S 表面处理
			①③④⑥	①③④⑥
MBK	整合型传动座	宽型	铸铁	发黑

产品特点: 使用之轴承经预压处理, 轴向往隙 0

B5  
滚珠丝杠  
支座组件



**订购编号示例**

①代号 - ②轴径 - ③适用法兰 - ④中心高  
**MBK - 15 - 60 - 32**

编号	名称	个数
1	传动座本体	1
2	轴承	1 组
3	压板	1
4	间隔环	2
5	油封	2
6	锁紧螺母	1 组

代码	型号				ΦD <sub>1</sub>	P.C.D	M	Z	B	P	L	J	E	E <sub>1</sub>	S	Q	H	H <sub>1</sub>	W <sub>1</sub>	T <sub>1</sub>	T <sub>2</sub>	T <sub>3</sub>	T <sub>4</sub>	M <sub>1</sub>	建议丝杠规格		建议电机规格																																																															
	适用丝杠轴径	适用电机法兰	中心高	适用类型																					支撑侧	止口规格	安装 P.C.D																																																															
	② d	③ F	④ h																																																																																							
MBK	15	60	30	伺服电机	50	70	M5	6	80	60	98	平底	38.5	46	11	17	50	35	40	22	6	36	10	M15×1.0	HQ-CSLK-15	50	70																																																															
		60S					36										CSAF-15																																																																									
		60	32				M5																																																																																			
		60S					M4																																													52	37	-																																				
		80	30				M6																																																																																			
		80S					M5																																																																									50	38	HQ-CSLK-15	70	90						
	80	32	M6																																																																																							
	80S		M5																																																																																52	37					CSAF-15	
	57	30	M4														步进电机	38.1							66.7																																																																	
	57																																																																																								32	50
	86	30	M6																																																																																							
	86																																																																																									32

▲轴承采用 P5 配对 DF 组装, 最适宜滚珠丝杠使用  
 ▲\* 带 S 为松下电机, 不帶为其他电机品牌

¥ 优惠价	1~9	10~
	100%	询价