

# 精制联轴器·十字滑块型


## 顶丝型



产品特点: 主体采用 S45C 发黑处理, 高扭矩, 高扭转刚性, 用于搅拌机, 粉碎机 etc.



①代号	轴套 M 材质	弹性体 M 材质	销	⑤ 表面处理
CGHSJ	S45C	FCD400	聚缩醛	发黑



### 订购编号示例

①代号	-	② D	-	③ L	-	④ c	-	⑤ d
CGHSJ	-	12	-	15	-	c3	-	d4

①代号	② D	③ L	④ c ⑤ d 可选范围																
CGHSJ	12	15	3	4	5	6													
	15	16.6	3	4	5	6	8												
	17	20.4	4	5	6	8	10												
	20	22	5	6	6.35	8	10	12											
	26	26.6	6	6.35	8	10	12	14	15										
	30	34	8	10	12	14	15	16	18										
	34	35	10	12	14	15	16	18	20										
	38	40.5	10	12	14	15	16	18	20	22									
	45	45.2	12	14	15	16	18	20	22	24	25								
	55	51	15	16	18	20	22	24	25	28	30								
70	58.6	18	20	22	24	25	28	30	35	38	40	42							

①代号	② D	F	M	紧固螺钉扭 矩 (N·m)	额定扭矩 (N·m)	容许偏心 (mm)	容许偏角 (°)	容许转速 (rpm)	惯性矩 (kg·m <sup>2</sup> )	重量 (g)
CGHSJ	12	2.6	M2.5	0.5	2.7	0.3	2	2000	2.0x10 <sup>-7</sup>	9
	15	2.7	M3	0.7	3.3	0.3	2	2000	5.5x10 <sup>-7</sup>	15
	17	3.35	M3	0.7	5.5	0.3	2	2000	1.1x10 <sup>-6</sup>	24
	20	3.5	M3	0.7	7.7	0.4	2	2000	2.3x10 <sup>-6</sup>	34
	26	4.5	M4	1.7	11	0.5	2	2000	8.1x10 <sup>-6</sup>	72
	30	6	M4	1.7	26	0.6	2	2000	1.8x10 <sup>-5</sup>	119
	34	6.5	M5	4	35	0.7	2	2000	3.1x10 <sup>-5</sup>	159
	38	7.5	M5	4	55	0.8	2	2000	5.5x10 <sup>-5</sup>	230
	45	7.5	M5	4	66	1	2	2000	1.2x10 <sup>-4</sup>	364
	55	8.5	M6	7	99	1.2	2	2000	3.0x10 <sup>-4</sup>	636
70	10	M8	15	176	1.4	2	2000	8.9x10 <sup>-4</sup>	1090	

▲以上参数由最大孔径测得。