

内六角圆柱头螺钉

超短头



■超短头




① 代号	类型	[M] 材质	[H] 硬度	[S] 表面处理	强度等级	
SPLAJ	超短头型	全牙	SCM435	32-39HRC	发黑	10.9
SPLBJ			SUS304	—	—	—

产品特点: 超短头、省空间、不易受障碍影响。

订购编号示例

① 代号	-	② M	-	③ L
SPLAJ	-	M5	-	L10



型号		③ L										P	D	K	S	h					
① 代号	② M											螺距									
SPLAJ	2	3	4	5	6	8	10	12	14	16	18	0.4	4	1.5	1.3	1.2					
	2.5	3	4	5	6	8	10	12	14	16	18	20	0.45	5	1.5	1.3	1.5				
	3	3	4	5	6	8	10	12	14	16	18	20	0.5	6	1.5	1.5	2				
	4	4	5	6	8	10	12	14	16	18	20	25	30	0.7	8	1.5	2	2.5			
	5	5	6	8	10	12	14	16	18	20	25	30	0.8	9	1.5	3	3				
	6	6	8	10	12	14	16	18	20	25	30	1	10	1.5	3	4					
	8	8	10	12	14	16	18	20	25	30	35	40	45	50	55	60	1.25	13	1.5	4	5
	10	8	10	12	14	16	18	20	25	30	35	40	45	50	55	60	1.5	15	1.5	5	5

型号		③ L										P	D	K	S	h					
① 代号	② M											螺距									
SPLBJ	2	3	4	5	6	8	10	12	14	16	18	0.4	4	1.5	1.3	1.2					
	2.5	3	4	5	6	8	10	12	14	16	18	20	0.45	5	1.5	1.3	1.5				
	3	3	4	5	6	8	10	12	14	16	18	20	0.5	6	1.5	1.5	2				
	4	4	5	6	8	10	12	14	16	18	20	25	30	0.7	8	1.5	2	2.5			
	5	5	6	8	10	12	14	16	18	20	25	30	0.8	9	1.5	3	3				
	6	6	8	10	12	14	16	18	20	25	30	1	10	1.5	3	4					
	8	8	10	12	14	16	18	20	25	30	35	40	45	50	55	60	1.25	13	1.5	4	5
	10	8	10	12	14	16	18	20	25	30	35	40	45	50	55	60	1.5	15	1.5	5	5

F6
垫片/螺母
吊环

分类
目录



返回
主目录

