




①代号	类型	[M] 材质	[S] 表面处理	强度等级
SPGA	等长双头螺栓	碳钢	发黑	8.8
SPGB		SUS304	—	—

产品特点: 高强度螺栓, 硬度高, 韧性好。

订购编号示例

①代号	-	② M	-	③ L
SPGA	-	M10	-	L60



型号		③ L													P 螺距				
①代号	② M																		
SPGA	8	50	60	70	80	90	100												1.25
	10	50	60	70	80	90	100	110	120	130	140								1.5
	12	50	60	70	80	90	100	110	120	130	140								1.75
	14	50	60	70	80	90	100	110	120	130	140								2.0
	16	50	60	70	80	90	100	110	120	130	140	160	170	180	190	200			2.0
	20	50	60	70	80	90	100	110	120	130	140	160	170	180	190	200			2.5
	22	50	60	70	80	90	100	110	120	130	140	160	170	180	190	200			2.5
	24	50	60	70	80	90	100	110	120	130	140	160	170	180	190	200			3.0

型号		③ L													P 螺距				
①代号	② M																		
SPGB	8	50	60	70	80	90													1.25
	10	50	60	70	80	90	100	110	120	130	140								1.5
	12	50	60	70	80	90	100	110	120	130	140								1.75
	14	50	60	70	80	90	100	110	120	130	140	150							2.0
	16	50	60	70	80	90	100	110	120	130	140	150	160						2.0
	20		60	70	80	90	100	110	120	130	140	150	160						2.5
	22				80	90	100	110	120	130	140								3.0
	24	50	60	70	80	90	100	110	120	130	140	160	170	180	190	200			3.0

F6
垫 螺
片 丝
吊 母
环