


①代号	M材质	S表面处理	配件
<b>RDAY</b>	A6061	本色阳极氧化	2个紧定螺钉(35CrMo四氧化三铁保护膜)



**双槽型 RDAY**

其余<sup>④</sup>

视角标准：第一视角




①代号 - ②D - ③R - ④dr - ⑤追加加工代码

RDAY - D40 - R1.6 - d7

RDAY - D28 - R2.1 - d10 - DS

①代号	主要尺寸																				
	②D	③R	④dr指定单位1mm	D <sub>1</sub>	D <sub>2</sub>	D <sub>3</sub>	L	B	W	附件紧定螺钉规格	M(粗牙)	适用圆皮带直径									
RDAY	15	1.1	3~8	12	13	17	14	3	4	M3×3	M3	2									
	20		4~10	16	18	22															
	30		4~12	20	28	32															
	20	1.6	3~10	16	17	22	16	3	5	M3×3	M3	3									
	30		5~12	27	32	18							3	6							
	40			37	42																
	45		5~20	30	42	47															
	23	2.1	5~12	20	19	25	18	3	6	M3×3	M3	4									
	28				24	30															
	30				26	32															
	40				36	42															
	45				5~18	25							41	47							
	48				5~20	30							44	50							
	28	2.6	5~12	20	23	30	20	3	7	M3×3	M3	5									
	40				35	42															
	50				5~20	30							45	52							
	28				3.1	5~20							30	22	30	22	3	8	M4×3	M4	6
	38													32	40						
	48													42	50						
	50													44	52						
60	54													62							
75	69	77																			
100	94	102																			
50	4.1	5~20	30	42	52	30	5	10	M5×4	M5	8										
60				52	62																
100				92	102																
60				50	62																
100	5.1	5~20	34	90	102	34	5	12	M5×4	M5	10										
140				142																	



⑤追加加工类型	外径缩短	
代号	<b>DS</b>	
示例图		
详细信息	切割外圆减少外径尺寸 皮带半径/R	
	适用R规格	DS
	1.1	D+0.8
	1.6	D+1.2
	2.1	D+1.6
	2.6	D+1.8
	仅适用于R=1.1-1.6-2.1-2.6的 产品外圆切割的加工面可能不进行表面处理	
指定方法	<b>DS</b>	