


悬臂销



★ 产品特点：侧板外螺纹安装，零件侧挡圈紧固，安装方便。


■ 六角型



①代号	②No	轴径		指定单位1mm			⑥M(粗牙)	W	(E)	MD(粗牙)
		D	公差g6	③B	④L	⑤H				
(螺纹长度固定型) CSPBHN CSPEHN CSPNHN	6	6	-0.004 -0.012			6 ~ 12	3	8	9.2	M 6
	8	8	-0.005		5 ~ 100	8 ~ 16	4	10	11.5	M 8
	10	10	-0.014			10 ~ 20	4 5 6	13	15	M10
	12	12						14	16.2	
	13	13		2 ~ 60			5 6 8			
	15	15	-0.006 -0.017			12 ~ 24		17	19.6	M12
(螺纹长度选择型) CSPBHNL CSPENHL CSPNHNL	16	16					6 8 10	19	21.9	
	17	17								
	18	18								
	20	20		10 ~ 100						M20
	20A	20				6 8 10 12		24	27.7	M16
	22	22								M20
	22A	22	-0.007 -0.020	4 ~ 60		20 ~ 40				M16
	25	25					8 10 12 16	27	31.2	M20
25A	25								M16	
30	30								M20	
30A	30					8 10 12 16 20	32	36.9	M16	

- ▲ 有些尺寸可能带中心孔。
- ▲ B、L的尺寸请参阅下表后指定。
- ▲ 仅螺纹长度选择型可指定H。
- ▲ 有关外螺纹的退刀槽尺寸参见外螺纹退刀槽加工尺寸表。

M	B+L	粗牙螺纹			
M	B+L	螺纹直径(M)	T	R	K
M 3	B+L≥11.5	3			2.1~2.4
M 4	B+L≥14.0	4	1.2~1.5	0.2~0.3	2.9~3.2
M 5	B+L≥16.2	5			3.9~4.1
M 6	B+L≥18.5	6			4.3~4.9
M 8	B+L≥23.5	8	1.5~2.5	0.2~0.6	6.3~6.6
M10	B+L≥28.5	10			8.1~8.3
M12	B+L≥35.5	12			9.8~10.1
M16	B+L≥45.0	16	1.5~3.0	0.2~1.0	13.6~13.8
M20	B+L≥55.0	20	1.5~4.0		17.0~17.2
		24	2.5~5.0	0.2~1.5	20.2~20.7
		30			26.0~26.2



交货期 **10**工作日

- ▲ 常州发货
- ▲ 部分产品型号 12 天发货，请以报价为准
- ▲ 遇特殊期间交期有变更

	标准订单	特殊订单
数量	1~100	101~
交货期	10 个工作日	现询

▲ 遇到特殊期间，货期会有变更，详情见官网通知。

