




Thermostat, ETR

- Description:** Thermostat with NC/NO contacts to manage temperature in panels. ETR202 with a normally closed contact for regulating heaters. ETR201 with a normally open contact for regulating cooling devices or signal devices. Sensor element thermostatic bimetal. Mounting clip for 35 mm DIN rail (EN 60715).
- Material:** Plastic according to UL94 V-0.
- Setting range:** 0°C to 60°C. Switching temperature difference less than 7°K, and switching point tolerance $\pm 4^{\circ}\text{K}$.
- Switch capacity:** 240V AC, 10(2)A. 120V AC, 15(2)A. 24V DC, 30W. Value in brackets for inductive load.
- Operating temperature:** -20 to +80°C.
- Service life:** > 100,000 cycles.
- Connection:** Screw terminal for cable (0.5 to 2.5 mm²).
- Protection:** IP 20.
- Approvals:** CE, EAC, cULus_UL Listed.
- Finish:** RAL 7035.
- Pack quantity:** 1 piece.



Description	Item no.
Normally opened contact	ETR201
Normally closed contact	ETR202



Electric diagram

