

ROLLER INSERT WITHOUT COLLAR

ROLLER INSERT WITH COLLAR




Note:

Roller inserts provide double the capacity of ball bearing inserts.

Torsion protection is provided by the customer.

2198.34.



2198.34. Roller insert without collar

Order No	d	Load capacity		Roller		
		m [daN]	diameter	e	t	
2198.34.020	20	50	10	10	30	
2198.34.024	24	80	13	14	38	
2198.34.030	30	125	16	20	44	
2198.34.040	40	200	19	30	53	




Note:

Roller inserts provide double the capacity of ball bearing inserts.

Torsion protection is provided by the customer.

2198.35.



2198.35. Roller insert with collar

Order No	d	Load capacity		Roller			
		m [daN]	diameter	e	t	l	
2198.35.020	20	50	10	25	3.5	31	
2198.35.024	24	80	13	30	4	39	
2198.35.030	30	125	16	35	5	45	
2198.35.040	40	200	19	50	6	54	