


滚轮导轨

2198.44.



说明:

滚轴导套可以提供双倍的承载力。它们可以使工具进行精确的直线运动。
与滚珠导套相比，滚轴导套也可以使用在模具底板中(架空安装)。

* T 型槽并非绝对必要

2198.44. 滚轮导轨

订购编号	a	起重能力 m [daN]	L	滚柱 数量	滚柱直径	f	b*	c*	h	x	y
2198.44.18.105	18	150	105	3	10	1.5	30	12	30	35	14.5
2198.44.18.140	18	200	140	4	10	1.5	30	12	30	35	14.5
2198.44.18.175	18	250	175	5	10	1.5	30	12	30	35	14.5
2198.44.18.210	18	300	210	6	10	1.5	30	12	30	35	14.5
2198.44.18.280	18	400	280	8	10	1.5	30	12	30	35	14.5
2198.44.18.350	18	500	350	10	10	1.5	30	12	30	35	14.5
2198.44.22.120	22	240	120	3	13	1.5	37	16	38	40	14.5
2198.44.22.160	22	320	160	4	13	1.5	37	16	38	40	14.5
2198.44.22.200	22	400	200	5	13	1.5	37	16	38	40	14.5
2198.44.22.240	22	480	240	6	13	1.5	37	16	38	40	14.5
2198.44.22.320	22	640	320	8	13	1.5	37	16	38	40	14.5
2198.44.22.400	22	800	400	10	13	1.5	37	16	38	40	14.5
2198.44.28.135	28	380	135	3	16	1.5	46	20	48	45	19
2198.44.28.180	28	500	180	4	16	1.5	46	20	48	45	19
2198.44.28.225	28	630	225	5	16	1.5	46	20	48	45	19
2198.44.28.270	28	750	270	6	16	1.5	46	20	48	45	19
2198.44.28.360	28	1000	360	8	16	1.5	46	20	48	45	19
2198.44.28.450	28	1250	450	10	16	1.5	46	20	48	45	19
2198.44.36.150	36	600	150	3	19	1.5	56	25	61	50	24.5
2198.44.36.200	36	800	200	4	19	1.5	56	25	61	50	24.5
2198.44.36.250	36	1000	250	5	19	1.5	56	25	61	50	24.5
2198.44.36.300	36	1200	300	6	19	1.5	56	25	61	50	24.5
2198.44.36.400	36	1600	400	8	19	1.5	56	25	61	50	24.5
2198.44.36.500	36	2000	500	10	19	1.5	56	25	61	50	24.5