



MISKY PRUŽINY DIN ISO 10069-2 PODLOŽKA

2441.3.



Příklad montáže



2441.3. Misky pružiny DIN ISO 10069-2

Pružina ϕ	16	20	25	32	40	50	63	80	100	125
d_1	20	25	30	40	50	60	80	100	120	150
d_5	6,5	8,5	10,5	13,5	13,5	16,5	16,5	20,5	20,5	26
s	4	4	5	5	5	6	6	8	8	8


Materiál:

Mosaz


Příklad objednávky:

Misky pružiny DIN ISO 10069-2	=	2441.3.
Průměr pružiny Pružina ϕ	50 mm	= 050
Objednací číslo	=	2441.3. 050

244.4.



Příklad montáže



244.4. Podložka

Pružina ϕ	16	20	25	32	40	50	63	80	100	125
d_1	20	26	32	40	50	60	80	100	120	150
d_5	6,5	8,5	10,5	13,5	13,5	16,5	16,5	20,5	20,5	26
s	1	1,5	2	2,5	2,5	3	3	4	4	5

Materiál:

St 37

Příklad objednávky:

Podložka	=	244.4.
Průměr pružiny Pružina ϕ	50 mm	= 050
Objednací číslo	=	244.4. 050