


SPRING PLUNGER, WITH SPRING LOADED PIN, WITH HEXAGON SOCKET, INCREASED SPRING FORCE



2472.04.



Material:

Sleeve: Free machining steel, burnished
 Pin: Free machining steel hardened, burnished
 Spring: Nirosta

Note:


For locking and for pressing upwards or downwards.
 Temperature operating range: max. 250°C
 Identification of increased spring force by two longitudinal marks on the sleeve.

2472.04. Spring plunger, with spring loaded pin, with hexagon socket, increased spring force

Order No	d ₁	d ₂	SW	l	s	Spring force [N]	
						initial	final
2472.04.006	M6	2.7	3	15	2	11	25
2472.04.008	M8	3.8	4	18	2	23	59
2472.04.010	M10	4.5	5	23	2.5	20	54
2472.04.012	M12	6	6	26	3.5	38	96
2472.04.016	M16	8.5	8	33	4.5	50	100
2472.04.020	M20	10	10	43	6.5	52	133
2472.04.024	M24	13	12	48	8	91	223



2472.34.



Material:

Sleeve: Inox 1.4305
 Pin: Inox 1.4305
 Spring: Nirosta

Note:

For locking and for pressing upwards or downwards.
 Temperature operating range: max. 250°C
 Identification of increased spring force by two longitudinal marks on the sleeve.

2472.34. Spring plunger, with spring loaded pin, with hexagon socket, increased spring force

Order No	d ₁	d ₂	SW	l	s	Spring force [N]	
						initial	final
2472.34.006	M6	2.7	3	15	2	11	25
2472.34.008	M8	3.8	4	18	2	23	59
2472.34.010	M10	4.5	5	23	2.5	20	54
2472.34.012	M12	6	6	26	3.5	38	96
2472.34.016	M16	8.5	8	33	4.5	50	100
2472.34.020	M20	10	10	43	6.5	52	133
2472.34.024	M24	13	12	48	8	91	223