


# CONVEYOR BELT, ELECTRICALLY CONTROLLED

2195.302.



## 2195.302. Conveyor belt, electrically controlled

b	1,000	1,250	1,500	1,750	2,000	2,250	2,500	2,750	3,000	3,250	3,500	3,750	4,000
a													
30								•	•	•	•	•	•
50								•	•	•	•	•	•
75						•	•	•	•	•	•	•	•
100						•	•	•	•	•	•	•	•
125				•	•	•	•	•	•	•	•	•	•
150				•	•	•	•	•	•	•	•	•	•
175			•	•	•	•	•	•	•	•	•	•	•
200			•	•	•	•	•	•	•	•	•	•	•
225		•	•	•	•	•	•	•	•	•	•	•	•
250		•	•	•	•	•	•	•	•	•	•	•	•
275	•	•	•	•	•	•	•	•	•	•	•	•	•
300	•	•	•	•	•	•	•	•	•	•	•	•	•

### Belt load:

Belt width a	kg per meter conveyed
30- 50- 75	4
100-125-150	7
175-200-225	10
250-275-300	15

For more information refer to description and ordering guidelines.

### Ordering Code (example):

Conveyor belt, electrically controlled	= 2195.
Typ 302	= 302.
Belt width	a = 100 mm = 100.
Nominal belt length	b = 2500 mm = 2500.
Belt speed	= 1
Motor voltage 400 V	= 3
Motor position	= 1
Motor controller	= 1
Order No.	= 2195.302. 100. 2500. 1 3 1 1