


## SPRING PLUNGER, WITH SPRING LOADED PIN, WITH SLOT, STANDARD SPRING FORCE

2472.05.



**2472.05. Spring plunger, with spring loaded pin, with slot, standard spring force**

Order No	d <sub>1</sub>	d <sub>2</sub>	l	s	Spring force [N]	
					initial	final
2472.05.004	4	1.8	9	1.5	4.5	12.5
2472.05.005	5	2.4	12	2	5	13
2472.05.006	6	2.7	14	2	6	17
2472.05.008	8	3.8	16	2	16	33
2472.05.010	10	4.5	19	2.5	19	42
2472.05.012	12	6.2	22	3.5	22	57
2472.05.016	16	8.5	24	4.5	38	78
2472.05.020	20	10	30	6.5	39	81
2472.05.024	24	13	34	8	72	155


**Material:**

Sleeve: Free machining steel, burnished  
 Pin: Free machining steel hardened, burnished  
 Spring: Nirosta

**Note:**

For locking and for pressing upwards or downwards.  
 Temperature operating range: max. 250°C

2472.35.



**2472.35. Spring plunger, with spring loaded pin, with slot, standard spring force**

Order No	d <sub>1</sub>	d <sub>2</sub>	l	s	Spring force [N]	
					initial	final
2472.35.004	4	1.8	9	1.5	4.5	12.5
2472.35.005	5	2.4	12	2	5	13
2472.35.006	6	2.7	14	2	6	17
2472.35.008	8	3.8	16	2	16	33
2472.35.010	10	4.5	19	2.5	19	42
2472.35.012	12	6.2	22	3.5	22	57
2472.35.016	16	8.5	24	4.5	38	78
2472.35.020	20	10	30	6.5	39	81
2472.35.024	24	13	34	8	72	155

**Material:**

Sleeve: Inox 1.4305  
 Pin: Inox 1.4305  
 Spring: Nirosta

**Note:**

For locking and for pressing upwards or downwards.  
 Temperature operating range: max. 250°C