



MATRIX WITHOUT COLLAR, CYLINDRICAL



2602.



2602. Matrix without collar, cylindrical

d ₁ , d ₅	d ₂	l	f	l ₁	16	19	22	25	28	32
1,8 - 3,2	8	3	1		●	●	●	●	●	●
2 - 5	10	3	1		●	●	●	●	●	●
3 - 7	13	3	1.5		●	●	●	●	●	●
5 - 8	16	5	1.5		●	●	●	●	●	●
7 - 11	20	5	1.5		●	●	●	●	●	●
11 - 16	25	5	2.5		●	●	●	●	●	●
16 - 19	32	7	2.5		●	●	●	●	●	●
19 - 28	40	7	2.5		●	●	●	●	●	●

Material:

HSS

Order No. 2602.3.

Hardness 64 ± 2 HRC

Execution:

Diameter d₂ and end faces ground.

Key flats parallel with reference axis "A" unless otherwise specified.

*d₁ = size over corners

With starting holes for wire-EDM as per 2601.

Ordering Code (example):

Matrix without collar, cylindrical	=	2602.3.
Mount diameter d ₂	20 mm =	020.
Length l ₁	16 mm =	016.
Cutting form Shape	square =	1.
Cutting form width a	320 =	0320.
Cutting form length b	320 =	0320
Order No	=	2602.3. 020. 016. 1. 0320. 0320