


冲头 带弹顶销



267.



267. 冲头 带弹顶销

d _{1 h6}	d ₃	k	l ₁	60	71	80	90	100
5	8	5		●	●	●	●	●
6	9	5		●	●	●	●	●
8	11	5		●	●	●	●	●
10	13	5		●	●	●	●	●
13	16	5		●	●	●	●	●
16	19	6.4		●	●	●	●	●
20	23	6.4		●	●	●	●	●
25	28	6.4		●	●	●	●	●

材料:

HSS

订购编号 267.3.

硬度:

杆部 64 ± 2 HRC

头部 52 ± 5 HRC

材料说明和其他材料见E章开头。

结构:

凸模头部热墩粗,用切入磨削法精磨支承面和凸模柄部。

订购示例:

冲头 带弹顶销	=	267.
材料 MAT	HSS	= 3.
轴径 d ₁	13 mm	= 1300.
长度 l ₁	60 mm	= 060
订购编号	=	267. 3.1300. 060