


快速更换型冲头，阶梯式，圆形，带弹顶销，重载荷用



2713.



2713. 快速更换型冲头，阶梯式，圆形，带弹顶销，重载荷用

d ₂ / 订购数字	d ₅	P	l ₁ / 订购数字	l (订货字母)	63 (C)	71 (D)	80 (E)	90 (F)	100 (G)	110 (H)	125 (J)
10 / (2)	10	5 - 9,9	13(1) 19(2)		●	●	●	●	●		
13 / (3)	12	6 - 12,9	13(1) 19(2)		●	●	●	●	●	●	●
16 / (4)	12	8 - 15,9	13(1) 19(2) 25(3)		●	●	●	●	●	●	●
20 / (5)	12	10 - 19,9	13(1) 19(2) 25(3)		●	●	●	●	●	●	●
25 / (6)	12	12 - 24,9	13(1) 19(2) 25(3)			●	●	●	●	●	●
32 / (7)	12	16 - 31,9	13(1) 19(2) 25(3)			●	●	●	●	●	●
40 / (9)	12	19 - 39,9	19(2) 25(3) 30(4)				●	●	●	●	●

*在 d₂ = 16/ 20 和 l = 63; l_{1最大} = 19

材料:


HSS
硬度 62 ± 2 HRC

结构:

精磨凸模柄部和凸模切削刃直径。
特别尺寸请洽询

订购示例:

2 7 1 3 . 3 C 1 . 0 5 5 0



形状: 圆形
P = Ø 5,5 mm
冲裁凸模长度: l₁
13 mm
长度: l
63 mm
直径: d₂
13 mm
型号:
重型
规格:
圆形
冲头:
有压紧销

= 0550
订购数字
= (1)
订货字母
= (C)
订购数字
= (3)
订购数字
= (3)
订购数字
= (1)
= 27