

符合DIN 59350带有加工余量的精密扁钢和精密方钢

2923.2099.




材料:

以 900-1050 N/mm² 对 1.2099 / X 5 CrS 12 抗腐蚀塑料 模具钢进行调质处理

结构:

厚度已精磨, 宽度已打磨或铣削, 长度已加工



2923.2099. 符合DIN 59350带有加工余量的精密扁钢和精密方钢

s	6.2	8.2	10.4	15.4	20.4	25.4	30.4	40.4	50.4
b									
20.3	●	●	●						
25.3	●	●	●	●					
30.3	●	●	●	●	●				
40.3	●	●	●	●	●	●			
50.3	●	●	●	●	●	●	●		
60.3	●	●	●	●	●	●	●	●	
80.3	●	●	●	●	●	●	●	●	●
100.3	●	●	●	●	●	●	●	●	●
125.3	●	●	●	●	●	●	●	●	●
150.3	●	●	●	●	●	●	●	●	●
200.3	●	●	●	●	●	●	●	●	●
250.3	●	●	●	●	●	●	●	●	●
300.3	●	●	●	●	●	●	●	●	●

订购示例:

符合DIN 59350带有加工余量的精密扁钢和精密方钢	=	2923.2099.
宽 B	80.3 mm =	080.
厚度 S	6.2 mm =	006.
长度 L	500 mm =	0500
订购编号	=	2923.2099. 080. 006. 0500